



## L1779

**Material**  
Aluminium.

**Technical Notes**  
For mounting of standard shaft diameters.

Order No.	d <sub>1</sub>	d <sub>2</sub>	d <sub>3</sub>	l <sub>1</sub> ±0,05	l <sub>2</sub>	l <sub>3</sub>	l <sub>4</sub>	w	l <sub>5</sub>	h <sub>1</sub>	h <sub>2</sub> ±0,02	h <sub>3</sub>	△ <sup>+</sup> △ <sub>g</sub>
L1779.008	8	5,5	M4	21	42	32	18	14	5,0	32,8	20	6	24
L1779.010	10	5,5	M4	21	42	32	18	14	5,0	32,8	20	6	24
L1779.012	12	5,5	M4	21	42	32	20	14	5,0	38,0	23	6	30
L1779.013	13	5,5	M4	21	42	32	20	14	5,0	38,0	23	6	30
L1779.016	16	5,5	M4	24	48	38	25	16	5,0	44,0	27	8	40
L1779.020	20	6,6	M5	30	60	45	30	20	7,5	51,0	31	10	70
L1779.025	25	6,6	M6	35	70	56	38	24	7,0	60,0	35	12	130
L1779.030	30	9,0	M6	42	84	64	44	28	10,0	70,0	42	12	180
L1779.035	35	11,0	M8	49	98	74	50	32	12,0	85,0	50	15	270
L1779.040	40	11,0	M8	57	114	90	60	36	12,0	96,0	60	15	420