



## L1779

**Material**  
Aluminium.

**Technical notes**

For mounting of standard shaft diameters.

Order No.	d <sub>1</sub>	d <sub>2</sub>	d <sub>3</sub>	l <sub>1</sub> ±0,05	l <sub>2</sub>	l <sub>3</sub>	l <sub>4</sub>	w	l <sub>5</sub>	h <sub>1</sub>	h <sub>2</sub> ±0,02	h <sub>3</sub>	Δ± g
<b>L1779.008</b>	8	5,5	M4	21	42	32	18	14	5,0	32,8	20	6	24
<b>L1779.010</b>	10	5,5	M4	21	42	32	18	14	5,0	32,8	20	6	24
<b>L1779.012</b>	12	5,5	M4	21	42	32	20	14	5,0	38,0	23	6	30
<b>L1779.013</b>	13	5,5	M4	21	42	32	20	14	5,0	38,0	23	6	30
<b>L1779.016</b>	16	5,5	M4	24	48	38	25	16	5,0	44,0	27	8	40
<b>L1779.020</b>	20	6,6	M5	30	60	45	30	20	7,5	51,0	31	10	70
<b>L1779.025</b>	25	6,6	M6	35	70	56	38	24	7,0	60,0	35	12	130
<b>L1779.030</b>	30	9,0	M6	42	84	64	44	28	10,0	70,0	42	12	180
<b>L1779.035</b>	35	11,0	M8	49	98	74	50	32	12,0	85,0	50	15	270
<b>L1779.040</b>	40	11,0	M8	57	114	90	60	36	12,0	96,0	60	15	420