



P2074

Material

Rubber (hardness - 55 Shore A).

Used in a wide range of vibrating machines. Allows high deformation with excellent spring back characteristics.

Supports axial and radial loads but not designed for traction or tension loads. For radial loads please contact our Technical Department.

Technical notes

Order No.	d_1	h	d_2	d_3	Compression max.	Max. axial load Kgf
P2074.095	95	88	23	30	28	200
P2074.100	100	110	20	30	36	500
P2074.144	144	122	40	23	48	1000
P2074.150	150	90	35	35	24	2000
P2074.155	155	150	30	25	64	2500
P2074.188	188	180	41	41	80	3500