



L1715

Material

Plastic body with hardened steel raceway segments.

Technical notes

For use with hardened shafts only (see part nos. L1770 - L1772) - tolerance h6.

Perpendicularity A is better than 15 μ .
Temperature range: -20°C to +80°C.

Tips

Easy assembly by press fitting, no additional retention is required when fitted into a bore with a tolerance of J6 or J7.

Order No.	d ₁ H6	d ₂ h6	l ±0,2	No. of ball circuits	Max. dynamic load C N	Max. static load C ₀ N	$\frac{\Delta C}{C}$ g
L1715.012	12	19	28	4	590	420	11,3
L1715.014	14	21	28	5	680	480	13,3
L1715.016	16	24	30	5	925	625	18,3
L1715.020	20	28	30	6	1170	800	22,1
L1715.025	25	35	40	6	2240	1500	51,2
L1715.030	30	40	50	6	3000	2240	70,6
L1715.040	40	52	60	7	5200	4050	90,2
L1715.050	50	62	70	8	6220	5880	110,2