



L1779.AL

Material

Aluminium (P40,6060)

Technical notes

For mounting of standard shaft diameters.

Order No.	d ₁	d ₂	d ₃	l ₁ ±0,05	l ₂	l ₃	l ₄	w	l ₅	h ₁	h ₂ ±0,02	h ₃	Δ± g
L1779.008-AL	8	5,5	M4	21	42	32	18	14	5,0	32,8	20	6	24
L1779.010-AL	10	5,5	M4	21	42	32	18	14	5,0	32,8	20	6	24
L1779.012-AL	12	5,5	M4	21	42	32	20	14	5,0	38,0	23	6	30
L1779.013-AL	13	5,5	M4	21	42	32	20	14	5,0	38,0	23	6	30
L1779.016-AL	16	5,5	M4	24	48	38	25	16	5,0	44,0	27	8	40
L1779.020-AL	20	6,6	M5	30	60	45	30	20	7,5	51,0	31	10	70
L1779.025-AL	25	6,6	M6	35	70	56	38	24	7,0	60,0	35	12	130
L1779.030-AL	30	9,0	M6	42	84	64	44	28	10,0	70,0	42	12	180
L1779.035-AL	35	11,0	M8	49	98	74	50	32	12,0	85,0	50	15	270
L1779.040-AL	40	11,0	M8	57	114	90	60	36	12,0	96,0	60	15	420