


## L1970.T

### Material

Steel (BS1449-HR1), zinc plated.

### Technical notes

Use hex. socket oval head screws (ISO 7380) or Torx screws (see part no. L1970.S).

Order No.	Rail size	$l_1$	h	$l_2$	$l_3$	$l_4$	$l_5$	$l_6$	$w_1$	$w_2$	$w_3$	$w_4$	For screw	 Kg
<b>L1970.20T-1040</b>	20	1040	19,2	80	40	7	5	2	10	2	7	3	M4	0,5
<b>L1970.20T-2080</b>	20	2080	19,2	80	40	7	5	2	10	2	7	3	M4	1,0
<b>L1970.20T-3120</b>	20	3120	19,2	80	40	7	5	2	10	2	7	3	M4	1,5
<b>L1970.30T-1040</b>	30	1040	29,5	80	40	8,4	6,4	2	15	2,5	10	4,5	M5	1,0
<b>L1970.30T-2080</b>	30	2080	29,5	80	40	8,4	6,4	2	15	2,5	10	4,5	M5	2,0
<b>L1970.30T-3120</b>	30	3120	29,5	80	40	8,4	6,4	2	15	2,5	10	4,5	M5	3,0
<b>L1970.45T-1040</b>	45	1040	46,4	80	40	11	9	2	24	4	15,5	6,5	M8	2,4
<b>L1970.45T-2080</b>	45	2080	46,4	80	40	11	9	2	24	4	15,5	6,5	M8	4,8
<b>L1970.45T-3120</b>	45	3120	46,4	80	40	11	9	2	24	4	15,5	6,5	M8	7,2