



R3091

Material

Stainless steel DIN 1,4305.

Technical notes

Order gears and clamps separately.

Order No.	Type	d ₁	d ₂ pin d ₂ clamp	d ₃	Adjustable slip torque Ncm
R3091.004-008-P	Pin	3,995	8	15	0 to 7
R3091.005-010-P	Pin	4,995	10	15	0 to 7
R3091.006-012-P	Pin	5,995	13	15	0 to 7
R3091.104-008-P	Pin	3,995	8	15	7 to 35
R3091.105-010-P	Pin	4,995	10	15	7 to 35
R3091.106-013-P	Pin	5,995	13	15	7 to 35
R3091.204-008-P	Pin	3,995	8	25	7 to 35
R3091.205-010-P	Pin	4,995	10	25	7 to 35
R3091.206-006-P	Pin	5,995	13	25	7 to 35
R3091.304-008-P	Pin	3,995	8	25	0 to 7
R3091.305-010-P	Pin	4,995	10	25	0 to 7
R3091.306-013-P	Pin	5,995	13	25	0 to 7
R3091.404-008-P	Pin	3,995	8	25	7 to 35
R3091.405-010-P	Pin	4,995	10	25	7 to 35
R3091.406-013-P	Pin	5,995	13	25	7 to 35
R3091.004-008-C	Clamp	3,995	8	25	7 to 35
R3091.005-010-C	Clamp	4,995	10	25	7 to 35
R3091.006-013-C	Clamp	5,995	13	25	7 to 35
R3091.104-008-C	Clamp	3,995	8	25	0 to 7
R3091.105-010-C	Clamp	4,995	10	25	0 to 7
R3091.106-013-C	Clamp	5,995	13	25	0 to 7
R3091.204-008-C	Clamp	3,995	8	25	7 to 35
R3091.205-010-C	Clamp	4,995	10	25	7 to 35
R3091.206-013-C	Clamp	5,995	13	25	7 to 35