





L3310

LINEAR TABLES

Material

Aluminium body blackened, steel knob.

Order No.	h_1	Load kg max.	Travel/rev	Travel distance	d_1	d_2	d_3	d_4	h_2	l_1	l_2	l_3
L3310.030	15	2.0	1° 25'	±2°	-	M 6x1	M2	2.5	2	30	24	-
L3310.060	20	4.0	0° 40'	±2°	-	M16x1	M4	4.5	4	60	50	-
L3310.090	23	5.0	0° 24'	±2°	114	M16x1	M4	4.5	4	90	50	-
L3310.125	30	5.0	0° 15'	±2°	114	M16x1	M4	4.5	4	125	50	25