




25mm Linear Guide Rail

standard, blackened

Linear Guide-
ways



L1016.BL25

LINEAR GUIDEWAYS

Material

Hardened and ground steel (typically 60 HRC). Black oxide.

part nos. L1016.F (flanged) and L1016.U (unflanged).

Other rail lengths on request.

Weight: 3,6 Kg/m.


Tips

Plastic screw covers issued with the rails to protect the holes from debris.

Technical Notes

For carriages to suit the required load see

Order No.	Rail size	l_1	h_1	l_2	w_1	l_3	h_2	d_1	d_2	For screws	Weight kg
L1016.BL25-0160	25	160	19.2	60	23	20	9	7	11	M 6	0.58
L1016.BL25-0220	25	220	19.2	60	23	20	9	7	11	M 6	0.79
L1016.BL25-0280	25	280	19.2	60	23	20	9	7	11	M 6	1.01
L1016.BL25-0340	25	340	19.2	60	23	20	9	7	11	M 6	1.22
L1016.BL25-0400	25	400	19.2	60	23	20	9	7	11	M 6	1.44
L1016.BL25-0460	25	460	19.2	60	23	20	9	7	11	M 6	1.66
L1016.BL25-0520	25	520	19.2	60	23	20	9	7	11	M 6	1.87
L1016.BL25-0580	25	580	19.2	60	23	20	9	7	11	M 6	2.09
L1016.BL25-0640	25	640	19.2	60	23	20	9	7	11	M 6	2.30
L1016.BL25-0700	25	700	19.2	60	23	20	9	7	11	M 6	2.52
L1016.BL25-0760	25	760	19.2	60	23	20	9	7	11	M 6	2.74
L1016.BL25-0820	25	820	19.2	60	23	20	9	7	11	M 6	2.95
L1016.BL25-0880	25	880	19.2	60	23	20	9	7	11	M 6	3.17
L1016.BL25-0940	25	940	19.2	60	23	20	9	7	11	M 6	3.38
L1016.BL25-1000	25	1000	19.2	60	23	20	9	7	11	M 6	3.60
L1016.BL25-1060	25	1060	19.2	60	23	20	9	7	11	M 6	3.82
L1016.BL25-1120	25	1120	19.2	60	23	20	9	7	11	M 6	4.03
L1016.BL25-1180	25	1180	19.2	60	23	20	9	7	11	M 6	4.25
L1016.BL25-1240	25	1240	19.2	60	23	20	9	7	11	M 6	4.46
L1016.BL25-1300	25	1300	19.2	60	23	20	9	7	11	M 6	4.68
L1016.BL25-1360	25	1360	19.2	60	23	20	9	7	11	M 6	4.90
L1016.BL25-1420	25	1420	19.2	60	23	20	9	7	11	M 6	5.11
L1016.BL25-1480	25	1480	19.2	60	23	20	9	7	11	M 6	5.33
L1016.BL25-1540	25	1540	19.2	60	23	20	9	7	11	M 6	5.54
L1016.BL25-1600	25	1600	19.2	60	23	20	9	7	11	M 6	5.76
L1016.BL25-1660	25	1660	19.2	60	23	20	9	7	11	M 6	5.98
L1016.BL25-1720	25	1720	19.2	60	23	20	9	7	11	M 6	6.19
L1016.BL25-1780	25	1780	19.2	60	23	20	9	7	11	M 6	6.41
L1016.BL25-1840	25	1840	19.2	60	23	20	9	7	11	M 6	6.62
L1016.BL25-1900	25	1900	19.2	60	23	20	9	7	11	M 6	6.84
L1016.BL25-1960	25	1960	19.2	60	23	20	9	7	11	M 6	7.06
L1016.BL25-2020	25	2020	19.2	60	23	20	9	7	11	M 6	7.27



Order No.	Rail size	l_1	h_1	l_2	w_1	l_3	h_2	d_1	d_2	For screws	Weight kg
L1016.BL25-2080	25	2080	19.2	60	23	20	9	7	11	M 6	7.49
L1016.BL25-2140	25	2140	19.2	60	23	20	9	7	11	M 6	7.70
L1016.BL25-2200	25	2200	19.2	60	23	20	9	7	11	M 6	7.92
L1016.BL25-2260	25	2260	19.2	60	23	20	9	7	11	M 6	8.14
L1016.BL25-2320	25	2320	19.2	60	23	20	9	7	11	M 6	8.35
L1016.BL25-2380	25	2380	19.2	60	23	20	9	7	11	M 6	8.57
L1016.BL25-2440	25	2440	19.2	60	23	20	9	7	11	M 6	8.78
L1016.BL25-2500	25	2500	19.2	60	23	20	9	7	11	M 6	9.00
L1016.BL25-2560	25	2560	19.2	60	23	20	9	7	11	M 6	9.22
L1016.BL25-2620	25	2620	19.2	60	23	20	9	7	11	M 6	9.43
L1016.BL25-2680	25	2680	19.2	60	23	20	9	7	11	M 6	9.65
L1016.BL25-2740	25	2740	19.2	60	23	20	9	7	11	M 6	9.86
L1016.BL25-2800	25	2800	19.2	60	23	20	9	7	11	M 6	10.08
L1016.BL25-2860	25	2860	19.2	60	23	20	9	7	11	M 6	10.30
L1016.BL25-2920	25	2920	19.2	60	23	20	9	7	11	M 6	10.51
L1016.BL25-2980	25	2980	19.2	60	23	20	9	7	11	M 6	10.73
L1016.BL25-3040	25	3040	19.2	60	23	20	9	7	11	M 6	10.94
L1016.BL25-3100	25	3100	19.2	60	23	20	9	7	11	M 6	11.16
L1016.BL25-3160	25	3160	19.2	60	23	20	9	7	11	M 6	11.38
L1016.BL25-3220	25	3220	19.2	60	23	20	9	7	11	M 6	11.59
L1016.BL25-3280	25	3280	19.2	60	23	20	9	7	11	M 6	11.81
L1016.BL25-3340	25	3340	19.2	60	23	20	9	7	11	M 6	12.02
L1016.BL25-3400	25	3400	19.2	60	23	20	9	7	11	M 6	12.24
L1016.BL25-3460	25	3460	19.2	60	23	20	9	7	11	M 6	12.46
L1016.BL25-3520	25	3520	19.2	60	23	20	9	7	11	M 6	12.67