





Aluminium Telescopic Slides

fully telescopic, size 70



L2044

TELESCOPIC SLIDES

Material

High quality grade aluminium (EN-AW-6082 T6, anodised), with steel ball bearings and cage.

yet robust telescopic slides (eg. aircraft seating).

Total length: = Installation length (l_1) + extension length (l_2).

major axis, with a load spread uniformly along the inner beam.

Technical Notes

Ideal for applications requiring lightweight

The maximum safe load is given for a fully extended pair of slides, mounted on the

Order No.	l_1	l_2 stroke	h_1	h_2	h_3	d_1	l_3	l_4	l_5	w_1	w_2	Load/pair kg max.
L2044.0400	400	400	70	45	25	M8	-	200	50	32	30	200
L2044.0450	450	450	70	45	25	M8	-	250	50	32	30	205
L2044.0500	500	500	70	45	25	M8	-	300	50	32	30	210
L2044.0550	550	550	70	45	25	M8	-	350	50	32	30	215
L2044.0600	600	600	70	45	25	M8	-	400	50	32	30	220
L2044.0650	650	650	70	45	25	M8	200	-	50	32	30	225
L2044.0700	700	700	70	45	25	M8	225	-	50	32	30	250
L2044.0750	750	750	70	45	25	M8	250	-	50	32	30	265
L2044.0800	800	800	70	45	25	M8	275	-	50	32	30	280
L2044.0850	850	850	70	45	25	M8	300	-	50	32	30	290
L2044.0900	900	900	70	45	25	M8	325	-	50	32	30	300
L2044.0950	950	950	70	45	25	M8	350	-	50	32	30	310
L2044.1000	1000	1000	70	45	25	M8	375	-	50	32	30	320
L2044.1050	1050	1050	70	45	25	M8	400	-	50	32	30	330
L2044.1100	1100	1100	70	45	25	M8	425	-	50	32	30	330
L2044.1150	1150	1150	70	45	25	M8	450	-	50	32	30	330
L2044.1200	1200	1200	70	45	25	M8	475	-	50	32	30	320
L2044.1250	1250	1250	70	45	25	M8	500	-	50	32	30	310
L2044.1300	1300	1300	70	45	25	M8	525	-	50	32	30	300
L2044.1350	1350	1350	70	45	25	M8	550	-	50	32	30	290
L2044.1400	1400	1400	70	45	25	M8	575	-	50	32	30	280
L2044.1450	1450	1450	70	45	25	M8	600	-	50	32	30	270
L2044.1500	1500	1500	70	45	25	M8	625	-	50	32	30	260
L2044.1550	1550	1550	70	45	25	M8	650	-	50	32	30	250
L2044.1600	1600	1600	70	45	25	M8	675	-	50	32	30	240
L2044.1650	1650	1650	70	45	25	M8	700	-	50	32	30	230
L2044.1700	1700	1700	70	45	25	M8	650	-	100	32	30	220
L2044.1750	1750	1750	70	45	25	M8	675	-	100	32	30	210
L2044.1800	1800	1800	70	45	25	M8	700	-	100	32	30	200
L2044.1850	1850	1850	70	45	25	M8	725	-	100	32	30	190



Order No.	l_1	l_2 stroke	h_1	h_2	h_3	d_1	l_3	l_4	l_5	w_1	w_2	Load/pair kg max.
L2044.1900	1900	1900	70	45	25	M8	750	-	100	32	30	180
L2044.1950	1950	1950	70	45	25	M8	775	-	100	32	30	170
L2044.2000	2000	2000	70	45	25	M8	800	-	100	32	30	160