


Lead Screw Linear Stages single carriage





L3147.S

Material

Aluminium body (anodised), with die cast zinc end plates. Steel lead screw with bronze nut. Stainless steel dust cover (AISI 304).

Technical Notes

Uses a 14 trapezoidal lead screw with 3mm

pitch.

Rigid, economical and light-weight. Can be used as a single in series, or a single or double unit in parallel, (connected via pulleys and belt drive). Ideal for slide adjustment on conveyors, fixtures, packing machines etc.

Tips

Often used in conjunction with one touch lock spindles, position indicators, handwheels etc.

Order No.	Travel I ₁	Rotation direction	l ₂	Weight kg
L3147.S150-L	150	Counter-clockwise	250	1.7
L3147.S200-R	200	Clockwise	300	1.9
L3147.S200-L	200	Counter-clockwise	300	1.9
L3147.S300-R	300	Clockwise	400	2.0
L3147.S300-L	300	Counter-clockwise	400	2.0
L3147.S150-R	150	Clockwise	250	1.7
L3147.S250-R	250	Clockwise	350	2.0
L3147.S250-L	250	Counter-clockwise	350	2.0



Lead Screw Driven Stages

End of travel and home switches



Limit and position switches:

End of Travel and/or Home Position switches can be installed onto these linear stages – please see the drawings of the brackets that attach to the stages that result from this requirement.

The End of Travel switch kit comes with two switches mounted to the base at each end – there are two flags mounted to the carriage. These flags are adjustable for either the full range of travel or a limit amounted.

The Home Position switch comes with one flag mounted to the base in the centre – with an adjustable flag mounted to the carriage, allowing the home position to be set at any point.

The switches are photoelectric sensors that operate on a supply voltage of 5 to 24V DC. The repeatability is 5 microns, the response time is 100 microseconds. The sensors are available in both NPN and PNP outputs. Quick fitting hook up cable (3 metres) provided.

Part no.	Order no.	Ls ₁	Ls ₂
L3141 Lead screw driven stage - Size 1			
HPS (home position switch)	L3141.025	50,8	38,1
	L3141.050	76.2	63,5
EOT (end of travel switches) 7.62 LS2	L3141.075	101,6	88,9
35.33 21.84 21.49 21.49 21.49 LS ₁ HPS (home position switch) EOT (end of travel switches)	L3141.110	152,4	139,7
L3142 Lead screw driven stage - Size 2 HPS (home position switch)	L3142.025	57,2	41,3
	L3142.038	76,2	60,3
EOT (end of travel switches)	L3142.050	88,9	73,0
37.0	L3142.075	108,0	92,1
.78 15.24 15.24 21.48 Ls ₁ 21.48 EOT (end of travel switches)	L3142.100	152,4	136,5
L3143 Lead screw driven stage - Size 3 HPS (home position switch)	L3143.025	76,2	60,3
	L3143.050	101,6	85,7
	L3143.075	127,0	111,1
	L3143.100	152,4	136,5
EOT (end of travel switches)	L3143.150	228,6	212,7
7.62	L3143.200	279,4	262,5
35.33 21.84 1 1 1 1 1 1 1 1 1 1 1 1 1 1 1 1 1 1 1	L3143.250	330,2	314,3
HPS (home position switch) EOT (end of travel)	L3143.300	381,0	365,1

