





Pozi Countersunk Machine Screws

Pozi - A4 stainless

Standard Screws



P0221.A4

STANDARD SCREWS

Material

Stainless steel A4.

Technical Notes

To DIN 965 H, ISO 7046. For the majority of


screw lengths the threads goes all the way to the head of the screw (i.e. $l_1 = l_2$) less 2.5 thread pitches.

For longer length screws the threaded

portion $l_2 < l_1$.

See technical page for tightening torques.

Order No.	d_1	l_1	d_2	l_2	h_1	Drive
P0221.016-003-A4	M1,6	3	3.0	-	0.96	PZ-0
P0221.016-004-A4	M1,6	4	3.0	-	0.96	PZ-0
P0221.016-005-A4	M1,6	5	3.0	-	0.96	PZ-0
P0221.016-006-A4	M1,6	6	3.0	-	0.96	PZ-0
P0221.016-008-A4	M1,6	8	3.0	-	0.96	PZ-0
P0221.016-010-A4	M1,6	10	3.0	-	0.96	PZ-0
P0221.016-012-A4	M1,6	12	3.0	-	0.96	PZ-0
P0221.016-014-A4	M1,6	14	3.0	-	0.96	PZ-0
P0221.016-016-A4	M1,6	16	3.0	-	0.96	PZ-0
P0221.020-003-A4	M 2	3	3.8	-	1.20	PZ-1
P0221.020-004-A4	M 2	4	3.8	-	1.20	PZ-1
P0221.020-005-A4	M 2	5	3.8	-	1.20	PZ-1
P0221.020-006-A4	M 2	6	3.8	-	1.20	PZ-1
P0221.020-008-A4	M 2	8	3.8	-	1.20	PZ-1
P0221.020-010-A4	M 2	10	3.8	-	1.20	PZ-1
P0221.020-012-A4	M 2	12	3.8	-	1.20	PZ-1
P0221.020-014-A4	M 2	14	3.8	-	1.20	PZ-1
P0221.020-016-A4	M 2	16	3.8	-	1.20	PZ-1
P0221.020-018-A4	M 2	18	3.8	16	1.20	PZ-1
P0221.020-020-A4	M 2	20	3.8	16	1.20	PZ-1
P0221.025-004-A4	M2,5	4	4.7	-	1.50	PZ-1
P0221.025-005-A4	M2,5	5	4.7	-	1.50	PZ-1
P0221.025-006-A4	M2,5	6	4.7	-	1.50	PZ-1
P0221.025-008-A4	M2,5	8	4.7	-	1.50	PZ-1
P0221.025-010-A4	M2,5	10	4.7	-	1.50	PZ-1
P0221.025-012-A4	M2,5	12	4.7	-	1.50	PZ-1
P0221.025-014-A4	M2,5	14	4.7	-	1.50	PZ-1
P0221.025-016-A4	M2,5	16	4.7	-	1.50	PZ-1
P0221.025-018-A4	M2,5	18	4.7	-	1.50	PZ-1
P0221.025-020-A4	M2,5	20	4.7	18	1.50	PZ-1
P0221.025-025-A4	M2,5	25	4.7	18	1.50	PZ-1
P0221.030-004-A4	M 3	4	5.6	-	1.65	PZ-1
P0221.030-005-A4	M 3	5	5.6	-	1.65	PZ-1
P0221.030-006-A4	M 3	6	5.6	-	1.65	PZ-1



Order No.	d ₁	l ₁	d ₂	l ₂	h ₁	Drive
P0221.030-008-A4	M 3	8	5.6	-	1.65	PZ-1
P0221.030-010-A4	M 3	10	5.6	-	1.65	PZ-1
P0221.030-012-A4	M 3	12	5.6	-	1.65	PZ-1
P0221.030-014-A4	M 3	14	5.6	-	1.65	PZ-1
P0221.030-016-A4	M 3	16	5.6	-	1.65	PZ-1
P0221.030-018-A4	M 3	18	5.6	-	1.65	PZ-1
P0221.030-020-A4	M 3	20	5.6	-	1.65	PZ-1
P0221.030-022-A4	M 3	22	5.6	19	1.65	PZ-1
P0221.030-025-A4	M 3	25	5.6	19	1.65	PZ-1
P0221.030-030-A4	M 3	30	5.6	19	1.65	PZ-1
P0221.030-035-A4	M 3	35	5.6	19	1.65	PZ-1
P0221.030-040-A4	M 3	40	5.6	19	1.65	PZ-1
P0221.030-045-A4	M 3	45	5.6	19	1.65	PZ-1
P0221.030-050-A4	M 3	50	5.6	19	1.65	PZ-1
P0221.030-055-A4	M 3	55	5.6	19	1.65	PZ-1
P0221.030-060-A4	M 3	60	5.6	19	1.65	PZ-1
P0221.040-005-A4	M 4	5	7.5	-	2.20	PZ-2
P0221.040-006-A4	M 4	6	7.5	-	2.20	PZ-2
P0221.040-008-A4	M 4	8	7.5	-	2.20	PZ-2
P0221.040-010-A4	M 4	10	7.5	-	2.20	PZ-2
P0221.040-012-A4	M 4	12	7.5	-	2.20	PZ-2
P0221.040-014-A4	M 4	14	7.5	-	2.20	PZ-2
P0221.040-016-A4	M 4	16	7.5	-	2.20	PZ-2
P0221.040-018-A4	M 4	18	7.5	-	2.20	PZ-2
P0221.040-020-A4	M 4	20	7.5	-	2.20	PZ-2
P0221.040-022-A4	M 4	22	7.5	-	2.20	PZ-2
P0221.040-025-A4	M 4	25	7.5	-	2.20	PZ-2
P0221.040-030-A4	M 4	30	7.5	22	2.20	PZ-2
P0221.040-035-A4	M 4	35	7.5	22	2.20	PZ-2
P0221.040-040-A4	M 4	40	7.5	22	2.20	PZ-2
P0221.040-045-A4	M 4	45	7.5	22	2.20	PZ-2
P0221.040-050-A4	M 4	50	7.5	22	2.20	PZ-2
P0221.040-055-A4	M 4	55	7.5	22	2.20	PZ-2
P0221.040-060-A4	M 4	60	7.5	22	2.20	PZ-2
P0221.040-065-A4	M 4	65	7.5	22	2.20	PZ-2
P0221.040-070-A4	M 4	70	7.5	22	2.20	PZ-2
P0221.040-075-A4	M 4	75	7.5	22	2.20	PZ-2
P0221.040-080-A4	M 4	80	7.5	22	2.20	PZ-2
P0221.040-085-A4	M 4	85	7.5	22	2.20	PZ-2
P0221.040-090-A4	M 4	90	7.5	22	2.20	PZ-2
P0221.040-095-A4	M 4	95	7.5	22	2.20	PZ-2
P0221.040-100-A4	M 4	100	7.5	22	2.20	PZ-2
P0221.050-006-A4	M 5	6	9.2	-	2.50	PZ-2
P0221.050-008-A4	M 5	8	9.2	-	2.50	PZ-2
P0221.050-010-A4	M 5	10	9.2	-	2.50	PZ-2
P0221.050-012-A4	M 5	12	9.2	-	2.50	PZ-2
P0221.050-014-A4	M 5	14	9.2	-	2.50	PZ-2
P0221.050-016-A4	M 5	16	9.2	-	2.50	PZ-2
P0221.050-018-A4	M 5	18	9.2	-	2.50	PZ-2
P0221.050-020-A4	M 5	20	9.2	-	2.50	PZ-2
P0221.050-022-A4	M 5	22	9.2	-	2.50	PZ-2
P0221.050-025-A4	M 5	25	9.2	-	2.50	PZ-2
P0221.050-030-A4	M 5	30	9.2	25	2.50	PZ-2
P0221.050-035-A4	M 5	35	9.2	25	2.50	PZ-2
P0221.050-040-A4	M 5	40	9.2	25	2.50	PZ-2
P0221.050-045-A4	M 5	45	9.2	25	2.50	PZ-2
P0221.050-050-A4	M 5	50	9.2	25	2.50	PZ-2
P0221.050-055-A4	M 5	55	9.2	25	2.50	PZ-2
P0221.050-060-A4	M 5	60	9.2	25	2.50	PZ-2
P0221.050-065-A4	M 5	65	9.2	25	2.50	PZ-2
P0221.050-070-A4	M 5	70	9.2	25	2.50	PZ-2
P0221.050-075-A4	M 5	75	9.2	25	2.50	PZ-2
P0221.050-080-A4	M 5	80	9.2	25	2.50	PZ-2
P0221.050-085-A4	M 5	85	9.2	25	2.50	PZ-2
P0221.050-090-A4	M 5	90	9.2	25	2.50	PZ-2
P0221.050-095-A4	M 5	95	9.2	25	2.50	PZ-2
P0221.050-100-A4	M 5	100	9.2	25	2.50	PZ-2
P0221.060-008-A4	M 6	8	11.0	-	3.00	PZ-3
P0221.060-010-A4	M 6	10	11.0	-	3.00	PZ-3



Pozi Countersunk Machine Screws

Pozi - A4 stainless

Standard Screws



Order No.	d ₁	l ₁	d ₂	l ₂	h ₁	Drive
P0221.060-012-A4	M 6	12	11.0	-	3.00	PZ-3
P0221.060-014-A4	M 6	14	11.0	-	3.00	PZ-3
P0221.060-016-A4	M 6	16	11.0	-	3.00	PZ-3
P0221.060-018-A4	M 6	18	11.0	-	3.00	PZ-3
P0221.060-020-A4	M 6	20	11.0	-	3.00	PZ-3
P0221.060-022-A4	M 6	22	11.0	-	3.00	PZ-3
P0221.060-025-A4	M 6	25	11.0	-	3.00	PZ-3
P0221.060-030-A4	M 6	30	11.0	-	3.00	PZ-3
P0221.060-035-A4	M 6	35	11.0	28	3.00	PZ-3
P0221.060-040-A4	M 6	40	11.0	28	3.00	PZ-3
P0221.060-045-A4	M 6	45	11.0	28	3.00	PZ-3
P0221.060-050-A4	M 6	50	11.0	28	3.00	PZ-3
P0221.060-055-A4	M 6	55	11.0	28	3.00	PZ-3
P0221.060-060-A4	M 6	60	11.0	28	3.00	PZ-3
P0221.060-065-A4	M 6	65	11.0	28	3.00	PZ-3
P0221.060-070-A4	M 6	70	11.0	28	3.00	PZ-3
P0221.060-075-A4	M 6	75	11.0	28	3.00	PZ-3
P0221.060-080-A4	M 6	80	11.0	28	3.00	PZ-3
P0221.060-085-A4	M 6	85	11.0	28	3.00	PZ-3
P0221.060-090-A4	M 6	90	11.0	28	3.00	PZ-3
P0221.060-095-A4	M 6	95	11.0	28	3.00	PZ-3
P0221.060-100-A4	M 6	100	11.0	28	3.00	PZ-3
P0221.080-012-A4	M 8	12	14.5	-	4.00	PZ-4
P0221.080-014-A4	M 8	14	14.5	-	4.00	PZ-4
P0221.080-016-A4	M 8	16	14.5	-	4.00	PZ-4
P0221.080-018-A4	M 8	18	14.5	-	4.00	PZ-4
P0221.080-020-A4	M 8	20	14.5	-	4.00	PZ-4
P0221.080-022-A4	M 8	22	14.5	-	4.00	PZ-4
P0221.080-025-A4	M 8	25	14.5	-	4.00	PZ-4
P0221.080-030-A4	M 8	30	14.5	-	4.00	PZ-4
P0221.080-035-A4	M 8	35	14.5	-	4.00	PZ-4
P0221.080-040-A4	M 8	40	14.5	34	4.00	PZ-4
P0221.080-045-A4	M 8	45	14.5	34	4.00	PZ-4
P0221.080-050-A4	M 8	50	14.5	34	4.00	PZ-4
P0221.080-055-A4	M 8	55	14.5	34	4.00	PZ-4
P0221.080-060-A4	M 8	60	14.5	34	4.00	PZ-4
P0221.080-065-A4	M 8	65	14.5	34	4.00	PZ-4
P0221.080-070-A4	M 8	70	14.5	34	4.00	PZ-4
P0221.080-075-A4	M 8	75	14.5	34	4.00	PZ-4
P0221.080-080-A4	M 8	80	14.5	34	4.00	PZ-4
P0221.080-085-A4	M 8	85	14.5	34	4.00	PZ-4
P0221.080-090-A4	M 8	90	14.5	34	4.00	PZ-4
P0221.080-095-A4	M 8	95	14.5	34	4.00	PZ-4
P0221.080-100-A4	M 8	100	14.5	34	4.00	PZ-4
P0221.100-020-A4	M10	20	18.0	-	5.00	PZ-4
P0221.100-022-A4	M10	22	18.0	-	5.00	PZ-4
P0221.100-025-A4	M10	25	18.0	-	5.00	PZ-4
P0221.100-030-A4	M10	30	18.0	-	5.00	PZ-4
P0221.100-035-A4	M10	35	18.0	-	5.00	PZ-4
P0221.100-040-A4	M10	40	18.0	-	5.00	PZ-4
P0221.100-045-A4	M10	45	18.0	-	5.00	PZ-4
P0221.100-050-A4	M10	50	18.0	40	5.00	PZ-4
P0221.100-055-A4	M10	55	18.0	40	5.00	PZ-4
P0221.100-060-A4	M10	60	18.0	40	5.00	PZ-4
P0221.100-065-A4	M10	65	18.0	40	5.00	PZ-4
P0221.100-070-A4	M10	70	18.0	40	5.00	PZ-4
P0221.100-075-A4	M10	75	18.0	40	5.00	PZ-4
P0221.100-080-A4	M10	80	18.0	40	5.00	PZ-4
P0221.100-085-A4	M10	85	18.0	40	5.00	PZ-4
P0221.100-090-A4	M10	90	18.0	40	5.00	PZ-4
P0221.100-095-A4	M10	95	18.0	40	5.00	PZ-4
P0221.100-100-A4	M10	100	18.0	40	5.00	PZ-4

STANDARD SCREWS