



P0339

FLAT WASHERS

Material
Polyamide.

diameter).
Type 2 - to DIN 125, without chamfer.

Technical Notes

Type 1 - to DIN 9021, ISO 7093 (3x thread

Order No.	For thread	Type	d ₁	d ₂	h ₁ min.
P0339.030-009	M 3	Standard	3.2	9	0.8
P0339.040-012	M 4	Standard	4.3	12	0.8
P0339.050-015	M 5	Standard	5.3	15	1.0
P0339.060-018	M 6	Standard	6.4	18	1.5
P0339.080-024	M 8	Standard	8.4	24	2.0
P0339.100-030	M10	Standard	10.5	30	2.5
P0339.120-037	M12	Standard	13.0	37	3.0
P0339.160-050	M16	Standard	17.0	50	3.0
P0339.180-056	M18	Standard	20.0	56	4.0
P0339.200-060	M20	Standard	22.0	60	4.0
P0339.240-072	M24	Standard	26.0	72	5.0
P0339.300-092	M30	Standard	33.0	92	6.0
P0339.360-110	M36	Standard	39.0	110	8.0
P0339.020-005	M 2	Small	2.2	5	0.3
P0339.025-006	M2,5	Small	2.7	6	0.5
P0339.030-007	M 3	Small	3.2	7	0.5
P0339.040-009	M 4	Small	4.3	9	0.8
P0339.050-010	M 5	Small	5.3	10	1.0
P0339.060-012	M 6	Small	6.4	12	1.6
P0339.080-016	M 8	Small	8.4	16	1.6
P0339.100-020	M10	Small	10.5	20	2.0
P0339.120-024	M12	Small	13.0	24	2.5
P0339.140-028	M14	Small	15.0	28	2.5
P0339.160-030	M16	Small	17.0	30	3.0
P0339.180-034	M18	Small	19.0	34	3.0
P0339.200-037	M20	Small	21.0	37	3.0
P0339.240-044	M24	Small	25.0	44	4.0
P0339.270-050	M27	Small	28.0	50	4.0
P0339.300-086	M30	Small	31.0	56	4.0