



P1350

OTHER MECHANICAL PARTS

Material

Stainless steel (AISI 440B, DIN 1.4112),
hardness C55-60.
Chrome steel (DIN 1.3505, AISI 52100,

100Cr6), hardness C32-60.

Diameter tolerance Grade 10, $\pm 6\mu$.
Diameter tolerance Grade 25, $\pm 12\mu$.

Technical Notes

Other tolerances and material on request.

Order No.	Material	d_1
P1350.002-SS	Stainless Steel	2 \pm 0,012
P1350.003-SS	Stainless Steel	3 \pm 0,012
P1350.004-SS	Stainless Steel	4 \pm 0,012
P1350.005-SS	Stainless Steel	5 \pm 0,012
P1350.006-SS	Stainless Steel	6 \pm 0,012
P1350.007-SS	Stainless Steel	7 \pm 0,012
P1350.008-SS	Stainless Steel	8 \pm 0,012
P1350.009-SS	Stainless Steel	9 \pm 0,012
P1350.010-SS	Stainless Steel	10 \pm 0,012
P1350.011-SS	Stainless Steel	11 \pm 0,012
P1350.002-CS	Chrome Steel	2 \pm 0,006
P1350.003-CS	Chrome Steel	3 \pm 0,006
P1350.004-CS	Chrome Steel	4 \pm 0,006
P1350.005-CS	Chrome Steel	5 \pm 0,006
P1350.006-CS	Chrome Steel	6 \pm 0,006
P1350.007-CS	Chrome Steel	7 \pm 0,006
P1350.008-CS	Chrome Steel	8 \pm 0,006
P1350.009-CS	Chrome Steel	9 \pm 0,006
P1350.010-CS	Chrome Steel	10 \pm 0,006
P1350.011-CS	Chrome Steel	11 \pm 0,006