



P2075

ANTI-VIBRATION COMPONENTS

Material

Rubber (hardness - Shore 55 A).

Technical Notes

Used in a wide range of vibrating

machines.

Allows high deformation with excellent spring back characteristics.

Supports axial and radial loads but not

designed for traction or tension loads. For radial loads please contact our technical team.

Order No.	d ₁	h ₁	d ₂
P2075.020-015	20	15	6
P2075.030-020	30	20	8
P2075.030-022	30	22	8
P2075.035-030	35	30	12
P2075.035-040	35	40	12
P2075.040-030	40	30	10
P2075.045-035	45	35	10
P2075.045-045	45	45	10
P2075.050-045	50	45	10
P2075.060-040	60	40	12
P2075.070-045	70	45	14
P2075.080-050	80	50	16
P2075.080-080	80	80	20
P2075.093-120	93	120	20
P2075.100-060	100	60	20
P2075.100-147	100	147	20
P2075.110-070	110	70	22
P2075.130-060	130	60	25
P2075.148-190	148	190	50
P2075.160-100	160	100	30
P2075.170-110	170	110	31
P2075.200-125	200	125	70
P2075.250-300	250	300	60