



P2110

ANTI-VIBRATION COMPONENTS

Material

Aluminium body with anti-corrosion coating, zinc plated steel thread.

Polyurethane compound, (Sylomer), resistant to oil.

Technical Notes

The Sylomer compound offers high isolation

capacity with small static deformation in all medium- high frequency ranges.

This mount incorporates an interlocking metal component that provide a fail-safe protection for mobile applicants.

The metal has anti-corrosive treatment for outdoor applications.

Temperature range -30°C to +70 °C.

Order No.	d ₁	d ₂	h ₅	l ₁	l ₂	d ₃	h ₁	h ₂	h ₃	h ₄	Load kg	Weight kg
P2110.010-0015	M10	28	60	67	52	6.5	45.5	38	13	26	0-50	0.31
P2110.010-0025	M10	28	60	67	52	6.5	45.5	38	13	26	0-50	0.31
P2110.010-0045	M10	28	60	67	52	6.5	45.5	38	13	26	0-50	0.31
P2110.010-0050	M10	28	60	67	52	6.5	45.5	38	13	26	0-50	0.31
P2110.010-0100	M10	28	60	67	52	6.5	45.5	38	13	26	50-100	0.31
P2110.012-0150	M12	25	60	80	67	6.5	56.0	48	13	40	100-150	0.46
P2110.012-0200	M12	25	60	80	67	6.5	56.0	48	13	40	150-200	0.46
P2110.012-0280	M12	40	60	108	90	8.5	72.0	55	15	25	170-280	0.98
P2110.012-0400	M12	40	60	108	90	8.5	72.0	55	15	25	280-400	0.98
P2110.014-0400	M14	40	60	108	90	8.5	72.0	55	15	25	280-400	0.98
P2110.014-0800	M14	65	60	155	125	12.5	95.0	80	22	28	460-800	2.46
P2110.016-1000	M16	65	60	155	125	12.5	95.0	80	22	28	800-1000	2.46
P2110.018-1200	M18	65	60	175	140	14	95.0	80	23	28	1000-1200	3.1
P2110.020-1500	M20	65	60	175	140	14	95.0	80	23	28	1200-1500	3.1
P2110.020-2000	M20	65	60	205	162	16	95.0	80	28	28	1500-2000	3.75