



## P4190

### Material

Steel, zinc plated or stainless steel (A4, AISI 316).

| Order No.    | Material  | d <sub>1</sub> | d <sub>2</sub> | l <sub>1</sub> | w <sub>1</sub> | w <sub>2</sub> | Weight<br>kg |
|--------------|-----------|----------------|----------------|----------------|----------------|----------------|--------------|
| P4190.040-ZP | Steel     | 4              | 7              | 40             | 4.0            | 6              | 0.01         |
| P4190.050-ZP | Steel     | 5              | 8              | 50             | 5.0            | 7              | 0.02         |
| P4190.060-ZP | Steel     | 6              | 9              | 60             | 6.5            | 8              | 0.03         |
| P4190.070-ZP | Steel     | 7              | 10             | 70             | 8.0            | 8              | 0.04         |
| P4190.080-ZP | Steel     | 8              | 10             | Mar-00         | 8.5            | 9              | 0.07         |
| P4190.090-ZP | Steel     | 9              | 12             | 90             | 9.5            | 10             | 0.09         |
| P4190.100-ZP | Steel     | 10             | 15             | 100            | 10.5           | 11             | 0.12         |
| P4190.120-ZP | Steel     | 11             | 18             | 120            | 11.5           | 16             | 0.18         |
| P4190.140-ZP | Steel     | 12             | 20             | 140            | 13.0           | 19             | 0.26         |
| P4190.160-ZP | Steel     | 13             | 22             | Jun-00         | 15.0           | 25             | 0.35         |
| P4190.180-ZP | Steel     | 14             | 23             | 180            | 16.0           | 28             | 0.48         |
| P4190.040-A4 | Stainless | 4              | 6              | 40             | 4.0            | 6              | 0.02         |
| P4190.050-A4 | Stainless | 5              | 8              | 50             | 5.0            | 7              | 0.02         |
| P4190.060-A4 | Stainless | 6              | 9              | Feb-00         | 6.5            | 8              | 0.03         |
| P4190.070-A4 | Stainless | 7              | 10             | 70             | 8.0            | 8              | 0.04         |
| P4190.080-A4 | Stainless | 8              | 12             | 78             | 8.5            | 9              | 0.07         |