



R3255

RIGID COUPLINGS

Material

Stainless steel (DIN 1,4005).

Order No.	l_1	d_1 $+0.025 -0.000$	d_2 for	l_2	h_1	w_1
R3255.030	6.4	3.0	M 4	15.9	6.4	4.8
R3255.040	6.4	4.0	M 4	15.9	6.4	4.8
R3255.050	6.4	5.0	M 4	15.9	7.9	4.8
R3255.060	6.7	6.0	M 4	15.9	7.9	4.8