Stainless Right Angle Drives - 3

Ø15 shafts



R2353

Material
Stainless steel (AISI 316) housing and shafts, seals - NBR. Spiral bevel gears from hardened steel.

Shafts are key-wayed.

Technical Notes
Normally used as speed reducers.

Max. radial loading 140N. Max. axial loading 50N.
Angular alignment: 15' to 30' of arc.

Order No.	Shaft dia. tol. f7	Ratio	Input shaft A kW max.	Output shaft B Nm max.	Output shaft C Nm max.	Weight kg
R2353.1	15	1:1	0.88	3	3	1.86
R2353.2	15	2:1	0.59	2	2	1.86