


# Bearings - "Oil-less"

plain and flanged



## L1806



**Material**  
Sintered bronze.

**Technical Notes**  
Ultra precision.

Order No.	Type	Shaft Size	Ød	ØD	A	ØB	C
L1806.03-06	Plain	3	3,0	6,0	2,5	8,0	0,5
L1806.03-08	Plain	3	3,0	8,0	3,0	10,0	0,5
L1806.03-10	Plain	3	3,0	10,0	4,0	12,0	1,0
L1806.04-08	Plain	4	4,0	8,0	4,0	10,0	1,0
L1806.05-12	Plain	5	5,0	12,0	4,0	14,0	1,0
L1806.05-13	Plain	5	5,0	13,0	5,0	14,0	1,0
L1806.05-10	Plain	5	5,0	10,0	5,0	12,0	1,0
L1806.06-16	Plain	6	6,0	16,0	5,0	18,0	1,0
L1806.06-10	Plain	6	6,0	10,0	5,0	12,0	1,0
L1806.08-16	Plain	8	8,0	16,0	6,0	18,0	1,0
L1806.10-19	Plain	10	10,0	19,0	7,0	21,0	1,5
L1806.12-20	Plain	12	12,0	20,0	8,0	22,0	1,5
L1806.03-06-F	Flanged	3	3,0	6,0	2,5	8,0	0,5
L1806.03-08-F	Flanged	3	3,0	8,0	3,0	10,0	0,5
L1806.03-10-F	Flanged	3	3,0	10,0	4,0	12,0	1,0
L1806.04-08-F	Flanged	4	4,0	8,0	4,0	10,0	1,0
L1806.05-12-F	Flanged	5	5,0	12,0	4,0	14,0	1,0
L1806.05-13-F	Flanged	5	5,0	13,0	5,0	14,0	1,0
L1806.05-10-F	Flanged	5	5,0	10,0	5,0	12,0	1,0
L1806.06-16-F	Flanged	6	6,0	16,0	5,0	18,0	1,0
L1806.06-10-F	Flanged	6	6,0	10,0	5,0	12,0	1,0
L1806.08-16-F	Flanged	8	8,0	16,0	6,0	18,0	1,0
L1806.10-19-F	Flanged	10	10,0	19,0	7,0	21,0	1,5
L1806.12-20-F	Flanged	12	12,0	20,0	8,0	22,0	1,5



linear and rotary motion components

# Automation