



P1024



Material

Stainless steel (AISI 302, DIN1.4300) with nylon tip.
Nylon tip in variety of colours.

Technical Notes


Self-locking.
Extra holding power for full face control.
Will not mar or damage shaft or part.
Nylon "soft tip" conforms to shape of shaft or part.

Tips

302 stainless steel provides good resistance to corrosion, it is soft and non-magnetic. Typically used in food and pharmaceutical applications. 302 stainless steel is not suitable for use in marine environments.

Nylon Tip Set Screws - hexagon head

stainless steel (AISI 302)



Order No.	Thread	L	C	A
P1024.02-03	M2	3,8	0,8	0,8
P1024.02-04	M2	4,8	0,8	0,8
P1024.02-05	M2	5,8	0,8	0,8
P1024.02-06	M2	6,8	0,8	0,8
P1024.03-03	M3	3,8	1,6	0,8
P1024.03-04	M3	4,8	1,6	0,8
P1024.03-05	M3	5,8	1,6	0,8
P1024.03-06	M3	6,8	1,6	0,8
P1024.04-05	M4	5,2	2,4	1,2
P1024.04-07	M4	7,2	2,4	1,2
P1024.04-11	M4	11,2	2,4	1,2
P1024.04-15	M4	15,2	2,4	1,2
P1024.05-07	M5	7,2	2,4	1,2
P1024.05-11	M5	11,2	2,4	1,2
P1024.05-15	M5	15,2	2,4	1,2
P1024.05-21	M5	21,2	2,4	1,2
P1024.06-07	M6	7,6	3,2	1,6
P1024.06-11	M6	11,6	3,2	1,6
P1024.06-17	M6	17,6	3,2	1,6
P1024.06-26	M6	26,6	3,2	1,6
P1024.08-08	M8	8,4	4,8	2,4
P1024.08-12	M8	12,4	4,8	2,4
P1024.08-18	M8	18,4	4,8	2,4
P1024.08-27	M8	27,4	4,8	2,4
P1024.10-14	M10	14,4	6,5	3,5
P1024.10-22	M10	22,4	6,5	3,5
P1024.10-23	M10	32,4	6,5	3,5



THREADED FASTENERS

