


Precision Captive Screws

stainless steel (AISI 303)



P1035



Material

stainless steel DIN 1.4305 (AISI303).

Technical Notes

303 stainless steel provides good resistance to corrosion, it is soft and non-magnetic. Typically used in food and pharmaceutical applications.

Tips

303 stainless steel is not suitable for use in marine environments.

Order No.	Head Style	L	M	H	ØE	ØD	Thread Tol.6g
P1035.S30	Slotted	6,75	4,5	2,0	2,14	5,2	M3x0,5
P1035.S31	Slotted	8,25	4,5	2,0	2,14	5,2	M3x0,5
P1035.S40	Slotted	9,75	6,0	2,8	2,89	7,0	M4x0,7
P1035.S41	Slotted	11,75	6,0	2,8	2,89	7,0	M4x0,7
P1035.S42	Slotted	12,75	6,0	2,8	2,89	7,0	M4x0,7
P1035.S50	Slotted	13,25	7,5	3,5	3,77	9,0	M5x0,8
P1035.S51	Slotted	14,25	7,5	3,5	3,77	9,0	M5x0,8
P1035.H30	Hex Socket	6,75	4,5	2,0	2,14	5,2	M3x0,5
P1035.H31	Hex Socket	8,25	4,5	2,0	2,14	5,2	M3x0,5
P1035.H40	Hex Socket	9,75	6,0	2,8	2,89	7,0	M4x0,7
P1035.H41	Hex Socket	11,75	6,0	2,8	2,89	7,0	M4x0,7
P1035.H42	Hex Socket	12,75	6,0	2,8	2,89	7,0	M4x0,7
P1035.H50	Hex Socket	13,25	7,5	3,5	3,77	9,0	M5x0,8
P1035.H51	Hex Socket	14,25	7,5	3,5	3,77	9,0	M5x0,8



linear and rotary motion components

Automation

