


Precision Captive Screws

stainless steel A2(AISI304)



P1035



Material

stainless steel A2(AISI304, DIN1.4305).

Technical Notes

Stainless steel A2 is a hard stainless steel, which may (in harsh conditions) exhibit slight signs of rusting.



Order No.	Head Style	L	M	H	ØE	ØD	Thread Tol.6g
P1035.S30	Slotted	6,75	4,5	2,0	2,14	5,2	M3x0,5
P1035.S31	Slotted	8,25	4,5	2,0	2,14	5,2	M3x0,5
P1035.S40	Slotted	9,75	6,0	2,8	2,89	7,0	M4x0,7
P1035.S41	Slotted	11,75	6,0	2,8	2,89	7,0	M4x0,7
P1035.S42	Slotted	12,75	6,0	2,8	2,89	7,0	M4x0,7
P1035.S50	Slotted	13,25	7,5	3,5	3,77	9,0	M5x0,8
P1035.S51	Slotted	14,25	7,5	3,5	3,77	9,0	M5x0,8
P1035.H30	Hex Socket	6,75	4,5	2,0	2,14	5,2	M3x0,5
P1035.H31	Hex Socket	8,25	4,5	2,0	2,14	5,2	M3x0,5
P1035.H40	Hex Socket	9,75	6,0	2,8	2,89	7,0	M4x0,7
P1035.H41	Hex Socket	11,75	6,0	2,8	2,89	7,0	M4x0,7
P1035.H42	Hex Socket	12,75	6,0	2,8	2,89	7,0	M4x0,7
P1035.H50	Hex Socket	13,25	7,5	3,5	3,77	9,0	M5x0,8
P1035.H51	Hex Socket	14,25	7,5	3,5	3,77	9,0	M5x0,8

THREADED FASTENERS

