


Clamp Cleats

stainless steel



P1092



Order No.	H ±0,08	Ref J	E	Ref F	G	Screw Size	K	L Max.
P1092.006	0,79	3,18	1,02	1,80	7,0	M3	9,90	1,73
P1092.007	1,57	3,18	1,02	2,59	7,0	M3	9,90	1,73
P1092.008	1,57	3,18	1,27	2,84	9,5	M3	9,90	1,73
P1092.009	1,57	3,18	1,60	3,18	9,5	M3	9,90	1,73
P1092.010	1,98	3,18	1,60	3,58	9,5	M3	9,90	1,73
P1092.011	2,36	3,18	1,02	3,38	9,5	M3	9,90	1,73
P1092.012	2,36	3,18	1,27	3,63	9,5	M3	9,90	1,73
P1092.013	2,36	3,18	1,60	3,96	9,5	M3	9,90	1,73
P1092.014	3,18	3,18	1,27	4,45	9,5	M3	9,90	1,73
P1092.015	3,96	3,18	1,02	4,98	9,5	M3	9,90	1,73
P1092.016	5,72	3,18	1,60	7,32	11,0	M3	9,90	1,73
P1092.017	6,35	3,18	1,60	7,92	15,0	M3	9,90	1,73

Material


Stainless steel A4(AISI316) DIN 1,4401, with nylon insert. Supplied with A2(AISI303) stainless steel screw (screws not supplied with P1092.019, .020, or .026).

Technical Notes

Quick release, faster clamping and self-locking.

Tips

Bolt circle: use the larger of the following two bolt circles:
add 6,86 to max. flange diameter
OR add 10,16 to max. groove base diameter.



THREADED FASTENERS