



L1338

Material

Steel (EN10277-3, 11SMnPb37).
Manufactured to ISO 2901/2903
(DIN103).

Technical notes

Used for low rotation speeds, manual control, for clamping or locking functions and for receiving dead weights.
The use of steel to steel contact surface is not suitable for motorised motion.

Tips

Standard nuts are right hand thread, single starts.
For use with steel or stainless steel lead screws, L1320, L1321, L1322, and L1323.

Order No.	Size	d 7H	Lead	Thread direction	A/F h11	l +0.0,-0.2	No. of starts	Contact surface mm ²	Δ _g Kg
L1338.R10-02	TR10x 2	10	2	Right	17	15	1	150	0,022
L1338.R10-04	TR10x 4	10	4	Right	17	15	2	150	0,022
L1338.R12-03	TR12x 3	12	3	Right	19	18	1	210	0,032
L1338.R12-06	TR12x 6	12	6	Right	19	18	2	210	0,032
L1338.R14-03	TR14x 3	14	3	Right	22	21	1	285	0,049
L1338.R14-06	TR14x 6	14	6	Right	22	21	2	285	0,049
L1338.R16-04	TR16x 4	16	4	Right	24	24	1	365	0,065
L1338.R16-08	TR16x 8	16	8	Right	24	24	2	365	0,065
L1338.R18-04	TR18x 4	18	4	Right	27	27	1	470	0,091
L1338.R18-08	TR18x 8	18	8	Right	27	27	2	470	0,091
L1338.R20-04	TR20x 4	20	4	Right	30	30	1	590	0,124
L1338.R20-08	TR20x 8	20	8	Right	30	30	2	590	0,124
L1338.R22-05	TR22x 5	22	5	Right	30	33	1	700	0,125
L1338.R22-10	TR22x10	22	5	Right	30	33	2	700	0,125
L1338.R24-05	TR24x 5	24	5	Right	36	36	1	845	0,219
L1338.R24-10	TR24x10	24	10	Right	36	36	2	845	0,219
L1338.R26-05	TR26x 5	26	5	Right	36	39	1	1005	0,216
L1338.R26-10	TR26x10	26	10	Right	36	39	2	1005	0,216
L1338.R28-05	TR28x 5	28	5	Right	41	42	1	1175	0,318
L1338.R28-10	TR28x10	28	5	Right	41	42	2	1175	0,318
L1338.R30-06	TR30x 6	30	6	Right	46	45	1	1335	0,445
L1338.R30-12	TR30x12	30	12	Right	55	54	2	1335	0,445
L1338.R32-06	TR32x 6	32	6	Right	50	48	1	1430	0,567
L1338.R32-12	TR32x12	32	6	Right	50	48	2	1430	0,567
L1338.R36-06	TR36x 6	36	6	Right	55	54	1	1950	0,708
L1338.R36-12	TR36x12	36	12	Right	55	54	2	1950	0,708
L1338.R40-07	TR40x 7	40	7	Right	60	60	1	2400	0,893
L1338.R40-14	TR40x14	40	14	Right	60	60	2	2400	0,893
L1338.R44-07	TR44x 7	44	7	Right	65	66	1	2940	1,538
L1338.R50-08	TR50x 8	50	8	Right	75	75	1	3790	1,889

Order No.	Size	d 7H	Lead	Thread direction	A/F h11	l +0.0,-0.2	No.of starts	Contact surface mm ²	⚖ Kg
L1338.R60-09	TR60x 9	60	9	Right	90	90	1	5490	3,227
L1338.L10-02	TR10x2	10	2	Left	17	15	1	150	0,022
L1338.L12-03	TR12x3	12	3	Left	19	18	1	210	0,032
L1338.L14-03	TR14x3	14	3	Left	22	21	1	285	0,049
L1338.L16-04	TR16x4	16	4	Left	24	24	1	365	0,065
L1338.L18-04	TR18x4	18	4	Left	27	27	1	470	0,091
L1338.L20-04	TR20x4	20	4	Left	30	30	1	590	0,124
L1338.L22-05	TR22x5	22	5	Left	30	33	1	700	0,125
L1338.L24-05	TR24x5	24	5	Left	36	36	1	845	0,219
L1338.L26-05	TR26x5	26	5	Left	36	39	1	1005	0,216
L1338.L28-05	TR28x5	28	5	Left	41	42	1	1175	0,318
L1338.L30-06	TR30x6	30	6	Left	46	45	1	1335	0,445
L1338.L32-06	TR32x6	32	6	Left	50	48	1	1430	0,567
L1338.L36-06	TR36x6	36	6	Left	55	54	1	1950	0,708
L1338.L40-07	TR40x7	40	7	Left	60	60	1	2400	0,893
L1338.L44-07	TR44x7	44	7	Left	65	66	1	2940	1,538
L1338.L50-08	TR50x8	50	8	Left	75	75	1	3790	1,889
L1338.L60-09	TR60x9	60	9	Left	90	90	1	5490	3,227