

L1712

Material

Hardened and ground body from bearing steel.
Single body resin retainer (POM).
Supplied with nitrile rubber (NBR) end-seals -UU as standard.


For use with hardened shafts only (see part nos. L1770 - L1772) - tolerance h6.
Perpendicularity A is better than 15 μ .
Temperature range: -20°C to +80°C.
Steel ball retainers can be supplied for higher temperature applications up to +120°C - with no end seals.

Please advise at time of ordering if this is required.

Tips

Nickel plated version with stainless steel balls (for corrosion resistance) on request - or stainless steel version no. L1713.

Technical notes

Order No.	d ₁ H6	d ₂ h6	l ₁	d ₃	l ₂	l ₃	No. of ball circuits	Max. dynamic load C N	Max. static load C ₀ N	 g
L1712.008	8	16	45	15,2	33,0	1,10	4	430	780	31
L1712.012	12	22	57	21,0	45,8	1,30	4	650	1200	80
L1712.016	16	26	70	24,9	49,8	1,30	5	1230	2350	145
L1712.020	20	32	80	30,3	61,0	1,60	5	1400	2750	180
L1712.025	25	40	112	38,0	82,0	1,85	6	1560	3140	440
L1712.030	30	47	123	44,5	104,2	1,85	6	2490	5490	580
L1712.040	40	62	154	59,0	121,2	2,15	6	3430	8040	1170
L1712.050	50	75	192	72,0	155,2	2,65	6	6080	15900	3100
L1712.060	60	90	211	86,5	170,0	3,15	6	7650	20000	3500