




P2040

Material


Rubber on silver zinc plated steel.

Technical Notes


With a bell-like base this unit is suitable

for supporting most applications, such as engine suspensions. It can also be used to carry horizontal loads.

Order No.	Shore hardness	d_1	l_1	d_2	h_1	Load kgf max.
P2040.050	50 A	55	23	M10	40	30
P2040.060	60 A	55	23	M10	40	60
P2040.070	70 A	55	23	M10	40	120



P2041



Material


Rubber on zinc plated steel.

Order No.	Type	d ₁	l ₁	d ₂	d ₃	h ₁	Compression max.	Static load kgf max.
P2041.050	Type 1	50	-	10.5	-	15	2.2	180
P2041.085	Type 1	85	-	10.5	-	15	1.6	450
P2041.155	Type 2	55	25	M12	-	16	2.2	180
P2041.185	Type 2	85	25	M12	-	16	1.6	450
P2041.225	Type 2	125	25	M12	-	16	2.2	800
P2041.550	Type 3	50	-	6.0	45	18	2	50
P2041.591	Type 3	91	-	6.5	86	18	2	350
P2041.638	Type 3	138	-	10.5	130	25	2.6	900



Anti-vibration Mounts rectangular

Anti-Vibration Components



P2042

ANTI-VIBRATION COMPONENTS

Material


Rubber on silver zinc plated steel (rubber hardness - 55 Shore A).

Technical Notes



Used to support machine tools and packing machinery.

Provides vibration isolation for frequencies higher than 20Hz.


Order No.	Type	d ₁	l ₁	h ₁	l ₂	l ₃	l ₄	w ₁	Axial load kgf max.	Compression max.
P2042.050	Type 1	M12	50	20	37	-	-	60	250	2
P2042.100	Type 1	M12	100	20	37	-	-	60	500	2
P2042.150	Type 1	M12	150	20	37	-	-	60	750	2
P2042.200	Type 1	M12	200	20	37	-	-	60	1000	2
P2042.550	Type 2	M12	50	23	37	85	115	60	250	2
P2042.600	Type 2	M12	100	23	37	135	165	60	500	2
P2042.650	Type 2	M12	150	23	37	185	215	60	750	2
P2042.700	Type 2	M12	200	23	37	235	265	60	1000	2



P2043



type 1



type 2

Material

Rubber on silver zinc plated steel (rubber hardness - 55 Shore A).


Technical Notes

Used where transverse loads are present.

Order No.	Type	d ₁	l ₁	h ₁	l ₂	l ₃	l ₄	w ₁	w ₂	Compression max.	Static load kgf max.
P2043.100	Type 1	13	100	20	-	-	-	130	-	2	850
P2043.550	Type 2	13	150	23	215	185	15	145	60	2	1300
P2043.600	Type 2	13	200	23	265	235	15	145	60	2	1700

Anti-vibration Mounts with through holes

Anti-Vibration Components



P2044

ANTI-VIBRATION COMPONENTS

Material

Rubber on silver zinc plated steel (rubber hardness - 55 Shore A).

Technical Notes

Type 1: M12 thread supplied as separate

item to be screwed in if required.


Type 2: A twin version of type 1 and so therefore take heavier loads.

The central hole in the rubber pad increases the flexibility of the unit - improving


anti-vibration properties.

Used where good deflection properties are needed and for isolating of frequencies higher than 10Hz.

Order No.	Type	d ₁	l ₁	d ₂	h ₁	l ₂	l ₃	l ₄	l ₅	w ₁	Axial load kgf max.	Compression max.
P2044.050	Type 1	M12	115	13	45	85	50	37	15	60	120	8
P2044.100	Type 1	M12	165	13	45	135	100	37	15	60	250	8
P2044.150	Type 1	M12	215	13	45	185	150	37	15	60	350	8
P2044.200	Type 1	M12	265	13	45	235	200	37	15	60	500	8
P2044.500	Type 2	-	165	13	45	135	100	-	15	130	500	8
P2044.550	Type 2	-	215	13	45	185	150	-	15	130	700	8
P2044.600	Type 2	-	265	13	45	235	200	-	15	130	1000	8



P2045



Material

Rubber on silver zincplated steel.

Tips

Particularly useful for fans, generators, motors etc.

Order No.	Shore hardness	d ₁	l ₁	d ₂	h ₁	h ₂	l ₂	l ₃	w ₁	Load kgf max.
P2045.070	70 A	M12	100	13	50	45	180	25	70	1000
P2045.055	55 A	M12	100	13	50	45	180	25	70	500
P2045.080	80 A	M12	100	13	50	45	180	25	70	1200