


# Shoulder Nuts - Cap Head

hex drive - 303 stainless

Shoulder Screws



## P0127.A2

### Material

Stainless steel (AISI 303, 1.4305).  
Tensile strength 550 N/mm<sup>2</sup>.  
Proof stress min. 190 N/mm<sup>2</sup>,

austenitic stainless steel.

### Technical notes

303 stainless steel provides good resistance to corrosion, it is mildly magnetic.

Order No.	d <sub>1</sub> +0,000 -0,025	l <sub>1</sub> +0,05 -0,00	d <sub>2</sub> tol. 6g	d <sub>3</sub>	h <sub>1</sub> +0,00 -0,05	l <sub>2</sub> +0,05 -0,00	A/F
P0127.040-006-A2	4	6	M 2	6	3	4	2
P0127.040-008-A2	4	8	M 2	6	3	4	2
P0127.040-010-A2	4	10	M 2	6	3	4	2
P0127.040-012-A2	4	12	M 2	6	3	4	2
P0127.040-014-A2	4	14	M 2	6	3	4	2
P0127.040-016-A2	4	16	M 2	6	3	4	2
P0127.040-018-A2	4	18	M 2	6	3	4	2
P0127.040-020-A2	4	20	M 2	6	3	4	2
P0127.050-008-A2	5	8	M 2,5	8	4	5	2,5
P0127.050-010-A2	5	10	M 2,5	8	4	5	2,5
P0127.050-012-A2	5	12	M 2,5	8	4	5	2,5
P0127.050-016-A2	5	16	M 2,5	8	4	5	2,5
P0127.050-020-A2	5	20	M 2,5	8	4	5	2,5
P0127.050-025-A2	5	25	M 2,5	8	4	5	2,5
P0127.060-008-A2	6	8	M 3	10	5	6	3
P0127.060-010-A2	6	10	M 3	10	5	6	3
P0127.060-012-A2	6	12	M 3	10	5	6	3
P0127.060-016-A2	6	16	M 3	10	5	6	3
P0127.060-020-A2	6	20	M 3	10	5	6	3
P0127.060-025-A2	6	25	M 3	10	5	6	3
P0127.060-030-A2	6	30	M 3	10	5	6	3
P0127.060-040-A2	6	40	M 3	10	5	6	3
P0127.060-050-A2	6	50	M 3	10	5	6	3
P0127.080-016-A2	8	16	M 3,5	12	6	11	4
P0127.080-020-A2	8	20	M 3,5	12	6	11	4
P0127.080-025-A2	8	25	M 3,5	12	6	11	4
P0127.080-030-A2	8	30	M 3,5	12	6	11	4
P0127.080-040-A2	8	40	M 3,5	12	6	11	4

Tel: 0333 207 4498

Created 2022-06-23

Email: sales@automotioncomponents.co.uk

Web: automotioncomponents.co.uk

**AUTOMOTION<sup>®</sup>**  
**COMPONENTS**

# Shoulder Nuts - Cap Head

hex drive - 303 stainless

## Shoulder Screws

Order No.	d <sub>1</sub> +0,000 -0,025	l <sub>1</sub> +0,05 -0,00	d <sub>2</sub> tol. 6g	d <sub>3</sub>	h <sub>1</sub> +0,00 -0,05	l <sub>2</sub> +0,05 -0,00	A/F
<b>P0127.080-050-A2</b>	8	50	M 3,5	12	6	11	4
<b>P0127.100-016-A2</b>	10	16	M 4	14	7	12	5
<b>P0127.100-020-A2</b>	10	20	M 4	14	7	12	5
<b>P0127.100-025-A2</b>	10	25	M 4	14	7	12	5
<b>P0127.100-030-A2</b>	10	30	M 4	14	7	12	5
<b>P0127.100-040-A2</b>	10	40	M 4	14	7	12	5
<b>P0127.120-025-A2</b>	12	25	M 5	20	8	16	6
<b>P0127.120-030-A2</b>	12	30	M 5	20	8	16	6
<b>P0127.120-040-A2</b>	12	40	M 5	20	8	16	6
<b>P0127.120-050-A2</b>	12	50	M 5	20	8	16	6