


# Shoulder Screws - Countersunk

hex drive - 316 stainless

Shoulder Screws



**P0128.A4**

## Material

Stainless steel (AISI 316, 1.440).  
Tensile strength 480 N/mm<sup>2</sup>.  
Proof stress min. 200 N/mm<sup>2</sup>,  
austenitic stainless steel.

## Technical notes

316 Stainless provides excellent  
corrosion resistance for use in highly  
caustic or marine environments. For  
more standard applications please

see our A2 range which is more cost  
effective.  
Non-magnetic.

Order No.	d <sub>1</sub> +0,000 -0,025	l <sub>1</sub> +0,05 -0,00	d <sub>2</sub> tol. g6	d <sub>3</sub>	l <sub>2</sub> +0,05 -0,00	h <sub>1</sub> +0,00 -0,05	A/F
P0128.040-010-A4	4	10	M 3	8	4	2,0	2
P0128.040-012-A4	4	12	M 3	8	4	2,0	2
P0128.040-014-A4	4	14	M 3	8	4	2,0	2
P0128.040-016-A4	4	16	M 3	8	4	2,0	2
P0128.040-018-A4	4	18	M 3	8	4	2,0	2
P0128.040-020-A4	4	20	M 3	8	4	2,0	2
P0128.040-025-A4	4	25	M 3	8	4	2,0	2
P0128.040-030-A4	4	30	M 3	8	4	2,0	2
P0128.050-010-A4	5	10	M 4	10	5	2,5	2,5
P0128.050-012-A4	5	12	M 4	10	5	2,5	2,5
P0128.050-016-A4	5	16	M 4	10	5	2,5	2,5
P0128.050-020-A4	5	20	M 4	10	5	2,5	2,5
P0128.050-025-A4	5	25	M 4	10	5	2,5	2,5
P0128.050-030-A4	5	30	M 4	10	5	2,5	2,5
P0128.050-035-A4	5	35	M 4	10	5	2,5	2,5
P0128.050-040-A4	5	40	M 4	10	5	2,5	2,5
P0128.060-010-A4	6	10	M 5	12	6	3,0	3
P0128.060-012-A4	6	12	M 5	12	6	3,0	3
P0128.060-016-A4	6	16	M 5	12	6	3,0	3
P0128.060-020-A4	6	20	M 5	12	6	3,0	3
P0128.060-025-A4	6	25	M 5	12	6	3,0	3
P0128.060-030-A4	6	30	M 5	12	6	3,0	3
P0128.060-035-A4	6	35	M 5	12	6	3,0	3
P0128.060-040-A4	6	40	M 5	12	6	3,0	3
P0128.080-010-A4	8	10	M 6	16	11	4,0	4
P0128.080-012-A4	8	12	M 6	16	11	4,0	4
P0128.080-016-A4	8	16	M 6	16	11	4,0	4

Tel: 0333 207 4498

Created 2022-06-23

Email: sales@automotioncomponents.co.uk

Web: automotioncomponents.co.uk

**AUTOMOTION<sup>®</sup>**  
**COMPONENTS**

# Shoulder Screws - Countersunk

hex drive - 316 stainless

Shoulder Screws

Order No.	d <sub>1</sub> +0,000 -0,025	l <sub>1</sub> +0,05 -0,00	d <sub>2</sub> tol. g6	d <sub>3</sub>	l <sub>2</sub> +0,05 -0,00	h <sub>1</sub> +0,00 -0,05	A/F
P0128.080-020-A4	8	20	M 6	16	11	4,0	4
P0128.080-025-A4	8	25	M 6	16	11	4,0	4
P0128.080-030-A4	8	30	M 6	16	11	4,0	4
P0128.080-035-A4	8	35	M 6	16	11	4,0	4
P0128.080-040-A4	8	40	M 6	16	11	4,0	4
P0128.100-012-A4	10	12	M 8	20	12	5,0	5
P0128.100-016-A4	10	16	M 8	20	12	5,0	5
P0128.100-020-A4	10	20	M 8	20	12	5,0	5
P0128.100-025-A4	10	25	M 8	20	12	5,0	5
P0128.100-030-A4	10	30	M 8	20	12	5,0	5
P0128.100-040-A4	10	40	M 8	20	12	5,0	5
P0128.100-050-A4	10	50	M 8	20	12	5,0	5
P0128.120-012-A4	12	12	M10	24	16	6,0	6
P0128.120-016-A4	12	16	M10	24	16	6,0	6
P0128.120-020-A4	12	20	M10	24	16	6,0	6
P0128.120-025-A4	12	25	M10	24	16	6,0	6
P0128.120-030-A4	12	30	M10	24	16	6,0	6
P0128.120-040-A4	12	40	M10	24	16	6,0	6
P0128.120-050-A4	12	50	M10	24	16	6,0	6