





L1790

LINEAR SHAFT SUPPORTS

Material
Steel (C40).

Technical Notes


For use with splined bushings part no.

L1791.


Torque figures stated are approximate, and dependent on the application. In important cases please consult our Tech-

nical department.

Order No.	No. of splines	d_1 +0.00 -0.08	d_2 +0.07 -0.27	l_1	r_1 45°	r_2	w_1 +0.00 -0.08	Section mm ²	Approx. torque Nm	Weight g
L1790.011-1.0	6	11	14	1000	0.2	0.2	3	121.9	38	0.9
L1790.013-1.0	6	13	16	1000	0.2	0.2	3.5	164.1	45	1.3
L1790.016-1.0	6	16	20	1000	0.2	0.2	5	243.4	101	1.9
L1790.018-1.0	6	18	22	1000	0.2	0.2	5	312.4	117	2.5
L1790.021-1.0	6	21	25	1000	0.2	0.2	5	399.8	130	3.1
L1790.023-1.0	6	23	28	1000	0.3	0.3	6	505.2	225	3.9
L1790.026-1.0	6	26	32	1000	0.3	0.3	6	638.6	310	5.0
L1790.032-1.0	8	32	38	1000	0.3	0.3	8	947.8	598	7.4
L1790.036-1.0	8	36	42	1000	0.3	0.3	7	1185.3	649	9.3
L1790.042-1.0	8	42	48	1000	0.3	0.3	8	1576.7	732	12.4
L1790.046-1.0	8	46	54	1000	0.5	0.3	9	1949.0	1095	15.3



L1791



Material

Steel (9 SMnPb 36).

Technical Notes

For use with splined shafts no. L1790.

Order No.	No. of splines	d_1	d_2	d_3 tol. h8	l_1	w_1	Weight kg
L1791.011-14	6	11	14	18.75	30	3	0.03
L1791.013-16	6	13	16	21.75	40	3.5	0.06
L1791.013-25	6	13	16	24.75	40	3.5	0.09
L1791.016-20	6	16	20	27.75	40	4	0.11
L1791.018-22	6	18	22	31.75	40	5	0.15
L1791.021-25	6	21	25	35.75	45	5	0.21
L1791.023-28	6	23	28	39.70	45	6	0.25
L1791.026-32	6	26	32	44.70	45	6	0.32
L1791.032-38	8	32	38	49.70	50	6	0.38
L1791.036-42	8	36	42	59.70	70	7	0.89
L1791.042-48	8	42	48	69.70	80	8	1.38
L1791.046-54	8	46	54	81.70	90	9	2.33