





# Stainless Dowel Pins A2 stainless



## Dowel Pins



## P1206

DOWEL PINS

### Material

Stainless steel (A2, AISI 303), chamfered end.

3-10mm long -  $\pm 0,25$   
12-50mm long -  $\pm 0,5$   
over 50mm long -  $\pm 0,75$ .

(P1207).

It is less resistant to corrosion, but less expensive than the A4 dowel pins.


### Technical Notes

To ISO 2338A (1997). Ground to m6 on  $\emptyset$ .  
 $l_1$  tolerances:

### Tips

A2 stainless steel grade is a harder material than the A4 stainless steel dowel pins

| Order No.     | $d_1$<br>tol. m6 | $l_1$ | $l_2$ | Double shear<br>kN |
|---------------|------------------|-------|-------|--------------------|
| P1206.010-003 | 1                | 3     | 0.2   | 0.7                |
| P1206.010-004 | 1                | 4     | 0.2   | 0.7                |
| P1206.010-005 | 1                | 5     | 0.2   | 0.7                |
| P1206.010-006 | 1                | 6     | 0.2   | 0.7                |
| P1206.010-008 | 1                | 8     | 0.2   | 0.7                |
| P1206.010-010 | 1                | 10    | 0.2   | 0.7                |
| P1206.010-012 | 1                | 12    | 0.2   | 0.7                |
| P1206.015-003 | 1.5              | 3     | 0.3   | 1.7                |
| P1206.015-004 | 1.5              | 4     | 0.3   | 1.7                |
| P1206.015-005 | 1.5              | 5     | 0.3   | 1.7                |
| P1206.015-006 | 1.5              | 6     | 0.3   | 1.7                |
| P1206.015-008 | 1.5              | 8     | 0.3   | 1.7                |
| P1206.015-010 | 1.5              | 10    | 0.3   | 1.7                |
| P1206.015-012 | 1.5              | 12    | 0.3   | 1.7                |
| P1206.015-014 | 1.5              | 14    | 0.3   | 1.7                |
| P1206.015-016 | 1.5              | 16    | 0.3   | 1.7                |
| P1206.015-018 | 1.5              | 18    | 0.3   | 1.7                |
| P1206.015-020 | 1.5              | 20    | 0.3   | 1.7                |
| P1206.015-024 | 1.5              | 24    | 0.3   | 1.7                |
| P1206.020-004 | 2                | 4     | 0.35  | 2.9                |
| P1206.020-005 | 2                | 5     | 0.35  | 2.9                |
| P1206.020-006 | 2                | 6     | 0.35  | 2.9                |
| P1206.020-008 | 2                | 8     | 0.35  | 2.9                |
| P1206.020-010 | 2                | 10    | 0.35  | 2.9                |
| P1206.020-012 | 2                | 12    | 0.35  | 2.9                |
| P1206.020-014 | 2                | 14    | 0.35  | 2.9                |
| P1206.020-016 | 2                | 16    | 0.35  | 2.9                |
| P1206.020-018 | 2                | 18    | 0.35  | 2.9                |
| P1206.020-020 | 2                | 20    | 0.35  | 2.9                |
| P1206.020-024 | 2                | 24    | 0.35  | 2.9                |
| P1206.025-004 | 2.5              | 4     | 0.4   | 4.4                |



| Order No.     | d <sub>1</sub><br>tol. m6 | l <sub>1</sub> | l <sub>2</sub> | Double shear<br>kN |
|---------------|---------------------------|----------------|----------------|--------------------|
| P1206.025-005 | 2.5                       | 5              | 0.4            | 4.4                |
| P1206.025-006 | 2.5                       | 6              | 0.4            | 4.4                |
| P1206.025-008 | 2.5                       | 8              | 0.4            | 4.4                |
| P1206.025-010 | 2.5                       | 10             | 0.4            | 4.4                |
| P1206.025-012 | 2.5                       | 12             | 0.4            | 4.4                |
| P1206.025-014 | 2.5                       | 14             | 0.4            | 4.4                |
| P1206.025-016 | 2.5                       | 16             | 0.4            | 4.4                |
| P1206.025-018 | 2.5                       | 18             | 0.4            | 4.4                |
| P1206.025-020 | 2.5                       | 20             | 0.4            | 4.4                |
| P1206.025-024 | 2.5                       | 24             | 0.4            | 4.4                |
| P1206.025-028 | 2.5                       | 28             | 0.4            | 4.4                |
| P1206.025-030 | 2.5                       | 30             | 0.4            | 4.4                |
| P1206.030-005 | 3                         | 5              | 0.5            | 6.6                |
| P1206.030-006 | 3                         | 6              | 0.5            | 6.6                |
| P1206.030-008 | 3                         | 8              | 0.5            | 6.6                |
| P1206.030-010 | 3                         | 10             | 0.5            | 6.6                |
| P1206.030-012 | 3                         | 12             | 0.5            | 6.6                |
| P1206.030-014 | 3                         | 14             | 0.5            | 6.6                |
| P1206.030-016 | 3                         | 16             | 0.5            | 6.6                |
| P1206.030-018 | 3                         | 18             | 0.5            | 6.6                |
| P1206.030-020 | 3                         | 20             | 0.5            | 6.6                |
| P1206.030-024 | 3                         | 24             | 0.5            | 6.6                |
| P1206.030-028 | 3                         | 28             | 0.5            | 6.6                |
| P1206.030-030 | 3                         | 30             | 0.5            | 6.6                |
| P1206.030-032 | 3                         | 32             | 0.5            | 6.6                |
| P1206.030-036 | 3                         | 36             | 0.5            | 6.6                |
| P1206.030-040 | 3                         | 40             | 0.5            | 6.6                |
| P1206.030-045 | 3                         | 45             | 0.5            | 6.6                |
| P1206.030-050 | 3                         | 50             | 0.5            | 6.6                |
| P1206.040-005 | 4                         | 5              | 0.63           | 11.7               |
| P1206.040-006 | 4                         | 6              | 0.63           | 11.7               |
| P1206.040-008 | 4                         | 8              | 0.63           | 11.7               |
| P1206.040-010 | 4                         | 10             | 0.63           | 11.7               |
| P1206.040-012 | 4                         | 12             | 0.63           | 11.7               |
| P1206.040-014 | 4                         | 14             | 0.63           | 11.7               |
| P1206.040-016 | 4                         | 16             | 0.63           | 11.7               |
| P1206.040-018 | 4                         | 18             | 0.63           | 11.7               |
| P1206.040-020 | 4                         | 20             | 0.63           | 11.7               |
| P1206.040-024 | 4                         | 24             | 0.63           | 11.7               |
| P1206.040-028 | 4                         | 28             | 0.63           | 11.7               |
| P1206.040-030 | 4                         | 30             | 0.63           | 11.7               |
| P1206.040-032 | 4                         | 32             | 0.63           | 11.7               |
| P1206.040-036 | 4                         | 36             | 0.63           | 11.7               |
| P1206.040-040 | 4                         | 40             | 0.63           | 11.7               |
| P1206.040-045 | 4                         | 45             | 0.63           | 11.7               |
| P1206.040-050 | 4                         | 50             | 0.63           | 11.7               |
| P1206.040-055 | 4                         | 55             | 0.63           | 11.7               |
| P1206.040-060 | 4                         | 60             | 0.63           | 11.7               |
| P1206.050-008 | 5                         | 8              | 0.8            | 18.1               |
| P1206.050-010 | 5                         | 10             | 0.8            | 18.1               |
| P1206.050-012 | 5                         | 12             | 0.8            | 18.1               |
| P1206.050-014 | 5                         | 14             | 0.8            | 18.1               |
| P1206.050-016 | 5                         | 16             | 0.8            | 18.1               |
| P1206.050-018 | 5                         | 18             | 0.8            | 18.1               |
| P1206.050-020 | 5                         | 20             | 0.8            | 18.1               |
| P1206.050-024 | 5                         | 24             | 0.8            | 18.1               |
| P1206.050-028 | 5                         | 28             | 0.8            | 18.1               |
| P1206.050-030 | 5                         | 30             | 0.8            | 18.1               |
| P1206.050-032 | 5                         | 32             | 0.8            | 18.1               |
| P1206.050-036 | 5                         | 36             | 0.8            | 18.1               |
| P1206.050-040 | 5                         | 40             | 0.8            | 18.1               |
| P1206.050-045 | 5                         | 45             | 0.8            | 18.1               |
| P1206.050-050 | 5                         | 50             | 0.8            | 18.1               |
| P1206.050-055 | 5                         | 55             | 0.8            | 18.1               |
| P1206.050-060 | 5                         | 60             | 0.8            | 18.1               |
| P1206.060-010 | 6                         | 10             | 1.2            | 26.0               |
| P1206.060-012 | 6                         | 12             | 1.2            | 26.0               |
| P1206.060-014 | 6                         | 14             | 1.2            | 26.0               |




# Stainless Dowel Pins A2 stainless



| Order No.     | d <sub>1</sub><br>tol. m6 | l <sub>1</sub> | l <sub>2</sub> | Double shear<br>kN |
|---------------|---------------------------|----------------|----------------|--------------------|
| P1206.060-016 | 6                         | 16             | 1.2            | 26.0               |
| P1206.060-018 | 6                         | 18             | 1.2            | 26.0               |
| P1206.060-020 | 6                         | 20             | 1.2            | 26.0               |
| P1206.060-024 | 6                         | 24             | 1.2            | 26.0               |
| P1206.060-028 | 6                         | 28             | 1.2            | 26.0               |
| P1206.060-030 | 6                         | 30             | 1.2            | 26.0               |
| P1206.060-032 | 6                         | 32             | 1.2            | 26.0               |
| P1206.060-036 | 6                         | 36             | 1.2            | 26.0               |
| P1206.060-040 | 6                         | 40             | 1.2            | 26.0               |
| P1206.060-045 | 6                         | 45             | 1.2            | 26.0               |
| P1206.060-050 | 6                         | 50             | 1.2            | 26.0               |
| P1206.060-055 | 6                         | 55             | 1.2            | 26.0               |
| P1206.060-060 | 6                         | 60             | 1.2            | 26.0               |
| P1206.060-070 | 6                         | 70             | 1.2            | 26.0               |
| P1206.060-080 | 6                         | 80             | 1.2            | 26.0               |
| P1206.080-010 | 8                         | 10             | 1.6            | 47.0               |
| P1206.080-012 | 8                         | 12             | 1.6            | 47.0               |
| P1206.080-014 | 8                         | 14             | 1.6            | 47.0               |
| P1206.080-016 | 8                         | 16             | 1.6            | 47.0               |
| P1206.080-018 | 8                         | 18             | 1.6            | 47.0               |
| P1206.080-020 | 8                         | 20             | 1.6            | 47.0               |
| P1206.080-024 | 8                         | 24             | 1.6            | 47.0               |
| P1206.080-028 | 8                         | 28             | 1.6            | 47.0               |
| P1206.080-030 | 8                         | 30             | 1.6            | 47.0               |
| P1206.080-032 | 8                         | 32             | 1.6            | 47.0               |
| P1206.080-036 | 8                         | 36             | 1.6            | 47.0               |
| P1206.080-040 | 8                         | 40             | 1.6            | 47.0               |
| P1206.080-045 | 8                         | 45             | 1.6            | 47.0               |
| P1206.080-050 | 8                         | 50             | 1.6            | 47.0               |
| P1206.080-055 | 8                         | 55             | 1.6            | 47.0               |
| P1206.080-060 | 8                         | 60             | 1.6            | 47.0               |
| P1206.080-070 | 8                         | 70             | 1.6            | 47.0               |
| P1206.080-080 | 8                         | 80             | 1.6            | 47.0               |
| P1206.080-090 | 8                         | 90             | 1.6            | 47.0               |
| P1206.080-100 | 8                         | 100            | 1.6            | 47.0               |
| P1206.080-120 | 8                         | 120            | 1.6            | 47.0               |
| P1206.100-012 | 10                        | 12             | 2.0            | 64.1               |
| P1206.100-014 | 10                        | 14             | 2.0            | 64.1               |
| P1206.100-016 | 10                        | 16             | 2.0            | 64.1               |
| P1206.100-018 | 10                        | 18             | 2.0            | 64.1               |
| P1206.100-020 | 10                        | 20             | 2.0            | 64.1               |
| P1206.100-024 | 10                        | 24             | 2.0            | 64.1               |
| P1206.100-028 | 10                        | 28             | 2.0            | 64.1               |
| P1206.100-030 | 10                        | 30             | 2.0            | 64.1               |
| P1206.100-032 | 10                        | 32             | 2.0            | 64.1               |
| P1206.100-036 | 10                        | 36             | 2.0            | 64.1               |
| P1206.100-040 | 10                        | 40             | 2.0            | 64.1               |
| P1206.100-045 | 10                        | 45             | 2.0            | 64.1               |
| P1206.100-050 | 10                        | 50             | 2.0            | 64.1               |
| P1206.100-055 | 10                        | 55             | 2.0            | 64.1               |
| P1206.100-060 | 10                        | 60             | 2.0            | 64.1               |
| P1206.100-065 | 10                        | 65             | 2.0            | 64.1               |
| P1206.100-070 | 10                        | 70             | 2.0            | 64.1               |
| P1206.100-080 | 10                        | 80             | 2.0            | 64.1               |
| P1206.100-090 | 10                        | 90             | 2.0            | 64.1               |
| P1206.100-100 | 10                        | 100            | 2.0            | 64.1               |
| P1206.100-120 | 10                        | 120            | 2.0            | 64.1               |
| P1206.120-016 | 12                        | 16             | 2.5            | 92.0               |
| P1206.120-018 | 12                        | 18             | 2.5            | 92.0               |
| P1206.120-020 | 12                        | 20             | 2.5            | 92.0               |
| P1206.120-024 | 12                        | 24             | 2.5            | 92.0               |
| P1206.120-028 | 12                        | 28             | 2.5            | 92.0               |
| P1206.120-030 | 12                        | 30             | 2.5            | 92.0               |
| P1206.120-032 | 12                        | 32             | 2.5            | 92.0               |
| P1206.120-036 | 12                        | 36             | 2.5            | 92.0               |
| P1206.120-040 | 12                        | 40             | 2.5            | 92.0               |
| P1206.120-045 | 12                        | 45             | 2.5            | 92.0               |
| P1206.120-050 | 12                        | 50             | 2.5            | 92.0               |

DOWEL PINS




| Order No.     | d <sub>1</sub><br>tol. m6 | l <sub>1</sub> | l <sub>2</sub> | Double shear<br>kN |
|---------------|---------------------------|----------------|----------------|--------------------|
| P1206.120-055 | 12                        | 55             | 2.5            | 92.0               |
| P1206.120-060 | 12                        | 60             | 2.5            | 92.0               |
| P1206.120-070 | 12                        | 70             | 2.5            | 92.0               |
| P1206.120-080 | 12                        | 80             | 2.5            | 92.0               |
| P1206.120-090 | 12                        | 90             | 2.5            | 92.0               |
| P1206.120-100 | 12                        | 100            | 2.5            | 92.0               |
| P1206.120-120 | 12                        | 120            | 2.5            | 92.0               |
| P1206.160-024 | 16                        | 24             | 3.0            | 160.0              |
| P1206.160-028 | 16                        | 28             | 3.0            | 160.0              |
| P1206.160-030 | 16                        | 30             | 3.0            | 160.0              |
| P1206.160-032 | 16                        | 32             | 3.0            | 160.0              |
| P1206.160-036 | 16                        | 36             | 3.0            | 160.0              |
| P1206.160-040 | 16                        | 40             | 3.0            | 160.0              |
| P1206.160-045 | 16                        | 45             | 3.0            | 160.0              |
| P1206.160-050 | 16                        | 50             | 3.0            | 160.0              |
| P1206.160-055 | 16                        | 55             | 3.0            | 160.0              |
| P1206.160-060 | 16                        | 60             | 3.0            | 160.0              |
| P1206.160-070 | 16                        | 70             | 3.0            | 160.0              |
| P1206.160-080 | 16                        | 80             | 3.0            | 160.0              |
| P1206.160-090 | 16                        | 90             | 3.0            | 160.0              |
| P1206.160-100 | 16                        | 100            | 3.0            | 160.0              |
| P1206.160-120 | 16                        | 120            | 3.0            | 160.0              |




# Stainless Dowel Pins

## A4 stainless



Dowel Pins



P1207

DOWEL PINS

### Material

Stainless steel (A4, AISI 316), rounded end.

### Technical Notes

To DIN 7. Ground to m6 on  $\varnothing$  (h8 over  $\varnothing$ 16mm).

Note: overall length is greater than nominal length (note dimension  $l_2$ ).

$l_1$  tolerances:

3-10mm long - +0.3,-0

12-50mm long - +0.5,-0


over 50mm long - +0.5,-0.

### Tips

A4 stainless steel grade is a softer material than the A2 stainless steel dowel pins (part no. P1206).

It is more resistant to corrosion, and more expensive than the A2 grade dowel pins.

| Order No.     | $d_1$<br>tol. m6 | $l_1$ | $l_2$ | $r_1$ | Double shear<br>kN |
|---------------|------------------|-------|-------|-------|--------------------|
| P1207.010-003 | 1                | 3     | 0.15  | 1     | 0.7                |
| P1207.010-004 | 1                | 4     | 0.15  | 1     | 0.7                |
| P1207.010-005 | 1                | 5     | 0.15  | 1     | 0.7                |
| P1207.010-006 | 1                | 6     | 0.15  | 1     | 0.7                |
| P1207.010-008 | 1                | 8     | 0.15  | 1     | 0.7                |
| P1207.010-010 | 1                | 10    | 0.15  | 1     | 0.7                |
| P1207.010-012 | 1                | 12    | 0.15  | 1     | 0.7                |
| P1207.010-014 | 1                | 14    | 0.15  | 1     | 0.7                |
| P1207.010-016 | 1                | 16    | 0.15  | 1     | 0.7                |
| P1207.015-003 | 1.5              | 3     | 0.23  | 1.6   | 1.7                |
| P1207.015-004 | 1.5              | 4     | 0.23  | 1.6   | 1.7                |
| P1207.015-005 | 1.5              | 5     | 0.23  | 1.6   | 1.7                |
| P1207.015-006 | 1.5              | 6     | 0.23  | 1.6   | 1.7                |
| P1207.015-008 | 1.5              | 8     | 0.23  | 1.6   | 1.7                |
| P1207.015-010 | 1.5              | 10    | 0.23  | 1.6   | 1.7                |
| P1207.015-012 | 1.5              | 12    | 0.23  | 1.6   | 1.7                |
| P1207.015-014 | 1.5              | 14    | 0.23  | 1.6   | 1.7                |
| P1207.015-016 | 1.5              | 16    | 0.23  | 1.6   | 1.7                |
| P1207.015-018 | 1.5              | 18    | 0.23  | 1.6   | 1.7                |
| P1207.015-020 | 1.5              | 20    | 0.23  | 1.6   | 1.7                |
| P1207.015-024 | 1.5              | 24    | 0.23  | 1.6   | 1.7                |
| P1207.020-004 | 2                | 4     | 0.3   | 2     | 2.9                |
| P1207.020-005 | 2                | 5     | 0.3   | 2     | 2.9                |
| P1207.020-006 | 2                | 6     | 0.3   | 2     | 2.9                |
| P1207.020-008 | 2                | 8     | 0.3   | 2     | 2.9                |
| P1207.020-010 | 2                | 10    | 0.3   | 2     | 2.9                |
| P1207.020-012 | 2                | 12    | 0.3   | 2     | 2.9                |
| P1207.020-014 | 2                | 14    | 0.3   | 2     | 2.9                |
| P1207.020-016 | 2                | 16    | 0.3   | 2     | 2.9                |
| P1207.020-018 | 2                | 18    | 0.3   | 2     | 2.9                |
| P1207.020-020 | 2                | 20    | 0.3   | 2     | 2.9                |




| Order No.     | d <sub>1</sub><br>tol. m6 | l <sub>1</sub> | l <sub>2</sub> | r <sub>1</sub> | Double shear<br>kN |
|---------------|---------------------------|----------------|----------------|----------------|--------------------|
| P1207.020-024 | 2                         | 24             | 0.3            | 2              | 2.9                |
| P1207.025-004 | 2.5                       | 4              | 0.4            | 2.5            | 4.4                |
| P1207.025-005 | 2.5                       | 5              | 0.4            | 2.5            | 4.4                |
| P1207.025-006 | 2.5                       | 6              | 0.4            | 2.5            | 4.4                |
| P1207.025-008 | 2.5                       | 8              | 0.4            | 2.5            | 4.4                |
| P1207.025-010 | 2.5                       | 10             | 0.4            | 2.5            | 4.4                |
| P1207.025-012 | 2.5                       | 12             | 0.4            | 2.5            | 4.4                |
| P1207.025-014 | 2.5                       | 14             | 0.4            | 2.5            | 4.4                |
| P1207.025-016 | 2.5                       | 16             | 0.4            | 2.5            | 4.4                |
| P1207.025-018 | 2.5                       | 18             | 0.4            | 2.5            | 4.4                |
| P1207.025-020 | 2.5                       | 20             | 0.4            | 2.5            | 4.4                |
| P1207.025-024 | 2.5                       | 24             | 0.4            | 2.5            | 4.4                |
| P1207.025-028 | 2.5                       | 28             | 0.4            | 2.5            | 4.4                |
| P1207.030-005 | 3                         | 5              | 0.45           | 3              | 6.6                |
| P1207.030-006 | 3                         | 6              | 0.45           | 3              | 6.6                |
| P1207.030-008 | 3                         | 8              | 0.45           | 3              | 6.6                |
| P1207.030-010 | 3                         | 10             | 0.45           | 3              | 6.6                |
| P1207.030-012 | 3                         | 12             | 0.45           | 3              | 6.6                |
| P1207.030-014 | 3                         | 14             | 0.45           | 3              | 6.6                |
| P1207.030-016 | 3                         | 16             | 0.45           | 3              | 6.6                |
| P1207.030-018 | 3                         | 18             | 0.45           | 3              | 6.6                |
| P1207.030-020 | 3                         | 20             | 0.45           | 3              | 6.6                |
| P1207.030-024 | 3                         | 24             | 0.45           | 3              | 6.6                |
| P1207.030-028 | 3                         | 28             | 0.45           | 3              | 6.6                |
| P1207.030-032 | 3                         | 32             | 0.45           | 3              | 6.6                |
| P1207.030-036 | 3                         | 36             | 0.45           | 3              | 6.6                |
| P1207.030-040 | 3                         | 40             | 0.45           | 3              | 6.6                |
| P1207.040-005 | 4                         | 5              | 0.6            | 4              | 11.7               |
| P1207.040-006 | 4                         | 6              | 0.6            | 4              | 11.7               |
| P1207.040-008 | 4                         | 8              | 0.6            | 4              | 11.7               |
| P1207.040-010 | 4                         | 10             | 0.6            | 4              | 11.7               |
| P1207.040-012 | 4                         | 12             | 0.6            | 4              | 11.7               |
| P1207.040-014 | 4                         | 14             | 0.6            | 4              | 11.7               |
| P1207.040-016 | 4                         | 16             | 0.6            | 4              | 11.7               |
| P1207.040-018 | 4                         | 18             | 0.6            | 4              | 11.7               |
| P1207.040-020 | 4                         | 20             | 0.6            | 4              | 11.7               |
| P1207.040-024 | 4                         | 24             | 0.6            | 4              | 11.7               |
| P1207.040-028 | 4                         | 28             | 0.6            | 4              | 11.7               |
| P1207.040-032 | 4                         | 32             | 0.6            | 4              | 11.7               |
| P1207.040-036 | 4                         | 36             | 0.6            | 4              | 11.7               |
| P1207.040-040 | 4                         | 40             | 0.6            | 4              | 11.7               |
| P1207.050-006 | 5                         | 6              | 0.75           | 5              | 18.1               |
| P1207.050-008 | 5                         | 8              | 0.75           | 5              | 18.1               |
| P1207.050-010 | 5                         | 10             | 0.75           | 5              | 18.1               |
| P1207.050-012 | 5                         | 12             | 0.75           | 5              | 18.1               |
| P1207.050-014 | 5                         | 14             | 0.75           | 5              | 18.1               |
| P1207.050-016 | 5                         | 16             | 0.75           | 5              | 18.1               |
| P1207.050-018 | 5                         | 18             | 0.75           | 5              | 18.1               |
| P1207.050-020 | 5                         | 20             | 0.75           | 5              | 18.1               |
| P1207.050-024 | 5                         | 24             | 0.75           | 5              | 18.1               |
| P1207.050-028 | 5                         | 28             | 0.75           | 5              | 18.1               |
| P1207.050-032 | 5                         | 32             | 0.75           | 5              | 18.1               |
| P1207.050-036 | 5                         | 36             | 0.75           | 5              | 18.1               |
| P1207.050-040 | 5                         | 40             | 0.75           | 5              | 18.1               |
| P1207.050-045 | 5                         | 45             | 0.75           | 5              | 18.1               |
| P1207.050-050 | 5                         | 50             | 0.75           | 5              | 18.1               |
| P1207.050-060 | 5                         | 60             | 0.75           | 5              | 18.1               |
| P1207.060-008 | 6                         | 8              | 0.9            | 6              | 26.0               |
| P1207.060-010 | 6                         | 10             | 0.9            | 6              | 26.0               |
| P1207.060-012 | 6                         | 12             | 0.9            | 6              | 26.0               |
| P1207.060-014 | 6                         | 14             | 0.9            | 6              | 26.0               |
| P1207.060-016 | 6                         | 16             | 0.9            | 6              | 26.0               |
| P1207.060-018 | 6                         | 18             | 0.9            | 6              | 26.0               |
| P1207.060-020 | 6                         | 20             | 0.9            | 6              | 26.0               |
| P1207.060-024 | 6                         | 24             | 0.9            | 6              | 26.0               |
| P1207.060-028 | 6                         | 28             | 0.9            | 6              | 26.0               |
| P1207.060-030 | 6                         | 30             | 0.9            | 6              | 26.0               |
| P1207.060-032 | 6                         | 32             | 0.9            | 6              | 26.0               |



# Stainless Dowel Pins

## A4 stainless



Dowel Pins

DOWEL PINS

| Order No.     | d <sub>1</sub><br>tol. m6 | l <sub>1</sub> | l <sub>2</sub> | r <sub>1</sub> | Double shear<br>kN |
|---------------|---------------------------|----------------|----------------|----------------|--------------------|
| P1207.060-036 | 6                         | 36             | 0.9            | 6              | 26.0               |
| P1207.060-040 | 6                         | 40             | 0.9            | 6              | 26.0               |
| P1207.060-045 | 6                         | 45             | 0.9            | 6              | 26.0               |
| P1207.060-050 | 6                         | 50             | 0.9            | 6              | 26.0               |
| P1207.060-055 | 6                         | 55             | 0.9            | 6              | 26.0               |
| P1207.060-060 | 6                         | 60             | 0.9            | 6              | 26.0               |
| P1207.060-070 | 6                         | 70             | 0.9            | 6              | 26.0               |
| P1207.060-080 | 6                         | 80             | 0.9            | 6              | 26.0               |
| P1207.080-008 | 8                         | 8              | 1.2            | 8              | 47.0               |
| P1207.080-010 | 8                         | 10             | 1.2            | 8              | 47.0               |
| P1207.080-012 | 8                         | 12             | 1.2            | 8              | 47.0               |
| P1207.080-014 | 8                         | 14             | 1.2            | 8              | 47.0               |
| P1207.080-016 | 8                         | 16             | 1.2            | 8              | 47.0               |
| P1207.080-018 | 8                         | 18             | 1.2            | 8              | 47.0               |
| P1207.080-020 | 8                         | 20             | 1.2            | 8              | 47.0               |
| P1207.080-024 | 8                         | 24             | 1.2            | 8              | 47.0               |
| P1207.080-028 | 8                         | 28             | 1.2            | 8              | 47.0               |
| P1207.080-030 | 8                         | 30             | 1.2            | 8              | 47.0               |
| P1207.080-032 | 8                         | 32             | 1.2            | 8              | 47.0               |
| P1207.080-036 | 8                         | 36             | 1.2            | 8              | 47.0               |
| P1207.080-040 | 8                         | 40             | 1.2            | 8              | 47.0               |
| P1207.080-045 | 8                         | 45             | 1.2            | 8              | 47.0               |
| P1207.080-050 | 8                         | 50             | 1.2            | 8              | 47.0               |
| P1207.080-055 | 8                         | 55             | 1.2            | 8              | 47.0               |
| P1207.080-060 | 8                         | 60             | 1.2            | 8              | 47.0               |
| P1207.080-070 | 8                         | 70             | 1.2            | 8              | 47.0               |
| P1207.080-080 | 8                         | 80             | 1.2            | 8              | 47.0               |
| P1207.080-090 | 8                         | 90             | 1.2            | 8              | 47.0               |
| P1207.080-100 | 8                         | 100            | 1.2            | 8              | 47.0               |
| P1207.080-110 | 8                         | 110            | 1.2            | 8              | 47.0               |
| P1207.080-120 | 8                         | 120            | 1.2            | 8              | 47.0               |
| P1207.100-014 | 10                        | 14             | 1.5            | 10             | 64.1               |
| P1207.100-016 | 10                        | 16             | 1.5            | 10             | 64.1               |
| P1207.100-018 | 10                        | 18             | 1.5            | 10             | 64.1               |
| P1207.100-020 | 10                        | 20             | 1.5            | 10             | 64.1               |
| P1207.100-024 | 10                        | 24             | 1.5            | 10             | 64.1               |
| P1207.100-028 | 10                        | 28             | 1.5            | 10             | 64.1               |
| P1207.100-030 | 10                        | 30             | 1.5            | 10             | 64.1               |
| P1207.100-032 | 10                        | 32             | 1.5            | 10             | 64.1               |
| P1207.100-036 | 10                        | 36             | 1.5            | 10             | 64.1               |
| P1207.100-040 | 10                        | 40             | 1.5            | 10             | 64.1               |
| P1207.100-045 | 10                        | 45             | 1.5            | 10             | 64.1               |
| P1207.100-050 | 10                        | 50             | 1.5            | 10             | 64.1               |
| P1207.100-055 | 10                        | 55             | 1.5            | 10             | 64.1               |
| P1207.100-060 | 10                        | 60             | 1.5            | 10             | 64.1               |
| P1207.100-070 | 10                        | 70             | 1.5            | 10             | 64.1               |
| P1207.100-080 | 10                        | 80             | 1.5            | 10             | 64.1               |
| P1207.100-090 | 10                        | 90             | 1.5            | 10             | 64.1               |
| P1207.100-100 | 10                        | 100            | 1.5            | 10             | 64.1               |
| P1207.100-110 | 10                        | 110            | 1.5            | 10             | 64.1               |
| P1207.100-120 | 10                        | 120            | 1.5            | 10             | 64.1               |
| P1207.120-024 | 12                        | 24             | 1.8            | 12             | 92.0               |
| P1207.120-028 | 12                        | 28             | 1.8            | 12             | 92.0               |
| P1207.120-030 | 12                        | 30             | 1.8            | 12             | 92.0               |
| P1207.120-032 | 12                        | 32             | 1.8            | 12             | 92.0               |
| P1207.120-036 | 12                        | 36             | 1.8            | 12             | 92.0               |
| P1207.120-040 | 12                        | 40             | 1.8            | 12             | 92.0               |
| P1207.120-045 | 12                        | 45             | 1.8            | 12             | 92.0               |
| P1207.120-050 | 12                        | 50             | 1.8            | 12             | 92.0               |
| P1207.120-055 | 12                        | 55             | 1.8            | 12             | 92.0               |
| P1207.120-060 | 12                        | 60             | 1.8            | 12             | 92.0               |
| P1207.120-070 | 12                        | 70             | 1.8            | 12             | 92.0               |
| P1207.120-080 | 12                        | 80             | 1.8            | 12             | 92.0               |
| P1207.120-090 | 12                        | 90             | 1.8            | 12             | 92.0               |
| P1207.120-100 | 12                        | 100            | 1.8            | 12             | 92.0               |
| P1207.120-110 | 12                        | 110            | 1.8            | 12             | 92.0               |
| P1207.120-120 | 12                        | 120            | 1.8            | 12             | 92.0               |