




Needle Roller Linear Cages

Ball & Needle Cages



L1004.HW25

BALL & NEEDLE CAGES

Material

Steel rollers (100Cr6, hardened to 60 HRC), aluminium retaining cage.

Tips

See technical pages for load rating calculations - based on rail size and number of rollers in the system cages.

Technical Notes

Supplied in max. 1 metre lengths.

Order No.	d_1 ± 0.001	p_1	h_1	l_1	w_1	No. of rollers (pairs)	Dyn. load C /pair of rollers N max.	To suit rail
L1004.HW25-0100	3	6	13.8	100	25	16	1250	L1004.35
L1004.HW25-0200	3	6	13.8	200	25	32	2500	L1004.35
L1004.HW25-0300	3	6	13.8	300	25	48	3750	L1004.35
L1004.HW25-0400	3	6	13.8	400	25	64	5000	L1004.35
L1004.HW25-0500	3	6	13.8	400	25	80	6250	L1004.35
L1004.HW25-0600	3	6	13.8	600	25	96	7500	L1004.35
L1004.HW25-0700	3	6	13.8	700	25	112	8750	L1004.35
L1004.HW25-0800	3	6	13.8	800	25	128	10000	L1004.35
L1004.HW25-0900	3	6	13.8	900	25	144	11250	L1004.35
L1004.HW25-1000	3	6	13.8	1000	25	160	12500	L1004.35