




Needle Roller Linear Cages

Ball & Needle Cages



L1004.HW30

BALL & NEEDLE CAGES

Material

Steel rollers (100Cr6, hardened to 60 HRC), aluminium retaining cage.

Tips

See technical pages for load rating calculations - based on rail size and number of rollers in the system cages.

Technical Notes

Supplied in max. 1 metre lengths.

Order No.	d_1 ± 0.001	p_1	h_1	l_1	w_1	No. of rollers (pairs)	Dyn. load C /pair of rollers N max.	To suit rail
L1004.HW30-0100	3.5	7	17.8	100	30	13	1850	L1004.45
L1004.HW30-0200	3.5	7	17.8	200	30	26	3700	L1004.45
L1004.HW30-0300	3.5	7	17.8	300	30	39	5500	L1004.45
L1004.HW30-0400	3.5	7	17.8	400	30	52	7400	L1004.45
L1004.HW30-0500	3.5	7	17.8	400	30	65	9250	L1004.45
L1004.HW30-0600	3.5	7	17.8	600	30	78	11100	L1004.45
L1004.HW30-0700	3.5	7	17.8	700	30	91	12950	L1004.45
L1004.HW30-0800	3.5	7	17.8	800	30	104	14800	L1004.45
L1004.HW30-0900	3.5	7	17.8	900	30	117	16650	L1004.45
L1004.HW30-1000	3.5	7	17.8	1000	30	130	18500	L1004.45