




L1007.030

BALL & NEEDLE CAGES

Material

Ball steel (100Cr6 to DIN 5401, class 3),
ball cage plastic (PA 12).

Can also be supplied with corrosion
resistant stainless balls (AISI 304) balls,
plastic balls (POM) or ceramic balls.

Order No.	d_1	p_1	h_1	l_1	w_1	d_2	No. of rollers
L1007.030-0100	3	4.2	7	100	1	3.2	24
L1007.030-0200	3	4.2	7	200	1	3.2	47
L1007.030-0300	3	4.2	7	300	1	3.2	71
L1007.030-0400	3	4.2	7	400	1	3.2	94
L1007.030-0500	3	4.2	7	500	1	3.2	118
L1007.030-0600	3	4.2	7	600	1	3.2	142
L1007.030-0700	3	4.2	7	700	1	3.2	165
L1007.030-0800	3	4.2	7	800	1	3.2	189
L1007.030-0900	3	4.2	7	900	1	3.2	213
L1007.030-1000	3	4.2	7	1000	1	3.2	237