




L1007.040

BALL & NEEDLE CAGES

Material

Ball steel (100Cr6 to DIN 5401, class 3),
ball cage plastic (PA 12).

Can also be supplied with corrosion resistant stainless balls (AISI 304) balls,
plastic balls (POM) or ceramic balls.

Order No.	d_1	p_1	h_1	l_1	w_1	d_2	No. of rollers
L1007.040-0100	4	5.8	6.3	100	1.3	4.2	18
L1007.040-0200	4	5.8	6.3	200	1.3	4.2	35
L1007.040-0300	4	5.8	6.3	300	1.3	4.2	52
L1007.040-0400	4	5.8	6.3	400	1.3	4.2	69
L1007.040-0500	4	5.8	6.3	500	1.3	4.2	86
L1007.040-0600	4	5.8	6.3	600	1.3	4.2	103
L1007.040-0700	4	5.8	6.3	700	1.3	4.2	120
L1007.040-0800	4	5.8	6.3	800	1.3	4.2	137
L1007.040-0900	4	5.8	6.3	900	1.3	4.2	154
L1007.040-1000	4	5.8	6.3	1000	1.3	4.2	172