




L1007.110

BALL & NEEDLE CAGES

Material

Ball steel (100Cr6 to DIN 5401, class 3),
ball cage plastic (PA 12).

Can also be supplied with corrosion resistant stainless balls (AISI 304) balls,
plastic balls (POM) or ceramic balls.

Order No.	d_1	p_1	h_1	l_1	w_1	d_2	No. of rollers
L1007.110-0100	11	14	13.7	100	2.5	11.2	7
L1007.110-0200	11	14	13.7	200	2.5	11.2	14
L1007.110-0300	11	14	13.7	300	2.5	11.2	21
L1007.110-0400	11	14	13.7	400	2.5	11.2	28
L1007.110-0500	11	14	13.7	500	2.5	11.2	35
L1007.110-0600	11	14	13.7	600	2.5	11.2	42
L1007.110-0700	11	14	13.7	700	2.5	11.2	49
L1007.110-0800	11	14	13.7	800	2.5	11.2	56
L1007.110-0900	11	14	13.7	900	2.5	11.2	63
L1007.110-1000	11	14	13.7	1000	2.5	11.2	70