




Linear Cage - Crossed Roller steel cage

Ball & Needle
Cages



L1008.020-AA

BALL & NEEDLE CAGES

Material

Steel rollers (100Cr6, class 3, hardened to 60 HRC) retaining cage steel.

Important Notes

For load ratings calculations the maximum recommended load is 1/3 of the max. static

load.

Order No.	d_1	p_1	h_1	l_1	w_1	No. of rollers	Dyn. load C N max.
L1008.020-AA-0100	2	4	5.5	100	0.3	24	2040
L1008.020-AA-0200	2	4	5.5	200	0.3	49	4165
L1008.020-AA-0300	2	4	5.5	300	0.3	74	6290
L1008.020-AA-0400	2	4	5.5	400	0.3	99	8415
L1008.020-AA-0500	2	4	5.5	500	0.3	124	10540
L1008.020-AA-0600	2	4	5.5	600	0.3	149	12665
L1008.020-AA-0700	2	4	5.5	700	0.3	174	14790
L1008.020-AA-0800	2	4	5.5	800	0.3	199	16915
L1008.020-AA-0900	2	4	5.5	900	0.3	224	19040
L1008.020-AA-1000	2	4	5.5	1000	0.3	249	21165