




Linear Cage - Crossed Roller

stainless steel cage

Ball & Needle
Cages



L1008.020-SS

BALL & NEEDLE CAGES

Material

Stainless rollers (440C), stainless cage (AISI 304).

Important Notes

For load ratings calculations the maximum recommended load is 1/3 of the max. static

load.

Order No.	d_1	p_1	h_1	l_1	w_1	No. of rollers	Dyn. load C N max.
L1008.020-SS-0100	2	4	5.5	100	0.3	24	7032
L1008.020-SS-0200	2	4	5.5	200	0.3	49	14357
L1008.020-SS-0300	2	4	5.5	300	0.3	74	21682
L1008.020-SS-0400	2	4	5.5	400	0.3	99	29007
L1008.020-SS-0500	2	4	5.5	500	0.3	124	36332
L1008.020-SS-0600	2	4	5.5	600	0.3	149	43657
L1008.020-SS-0700	2	4	5.5	700	0.3	174	50982
L1008.020-SS-0800	2	4	5.5	800	0.3	199	58307
L1008.020-SS-0900	2	4	5.5	900	0.3	224	65632
L1008.020-SS-1000	2	4	5.5	1000	0.3	249	72957