




Linear Cage - Crossed Roller steel cage

Ball & Needle
Cages



L1008.030-AA

BALL & NEEDLE CAGES

Material

Steel rollers (100Cr6, class 3, hardened to 60 HRC) retaining cage steel.

Important Notes

For load ratings calculations the maximum recommended load is 1/3 of the max. static

load.

Order No.	d_1	p_1	h_1	l_1	w_1	No. of rollers	Dyn. load C N max.
L1008.030-AA-0100	3	5	7.5	100	0.4	19	2470
L1008.030-AA-0200	3	5	7.5	200	0.4	39	5070
L1008.030-AA-0300	3	5	7.5	300	0.4	59	7670
L1008.030-AA-0400	3	5	7.5	400	0.4	79	10270
L1008.030-AA-0500	3	5	7.5	500	0.4	99	12870
L1008.030-AA-0600	3	5	7.5	600	0.4	119	15470
L1008.030-AA-0700	3	5	7.5	700	0.4	139	18070
L1008.030-AA-0800	3	5	7.5	800	0.4	159	20670
L1008.030-AA-0900	3	5	7.5	900	0.4	179	23270
L1008.030-AA-1000	3	5	7.5	1000	0.4	199	25870