




Linear Cage - Crossed Roller steel cage

Ball & Needle
Cages



L1008.060-AA

BALL & NEEDLE CAGES

Material

Steel rollers (100Cr6, class 3, hardened to 60 HRC) retaining cage steel.

Important Notes

For load ratings calculations the maximum recommended load is 1/3 of the max. static

load.

Order No.	d_1	p_1	h_1	l_1	w_1	No. of rollers	Dyn. load C N max.
L1008.060-AA-0100	6	12	14	100	0.8	7	3887
L1008.060-AA-0200	6	12	14	200	0.8	16	8303
L1008.060-AA-0300	6	12	14	300	0.8	24	12720
L1008.060-AA-0400	6	12	14	400	0.8	32	17137
L1008.060-AA-0500	6	12	14	500	0.8	41	21553
L1008.060-AA-0600	6	12	14	600	0.8	49	25970
L1008.060-AA-0700	6	12	14	700	0.8	57	30387
L1008.060-AA-0800	6	12	14	800	0.8	66	34803
L1008.060-AA-0900	6	12	14	900	0.8	74	39220
L1008.060-AA-1000	6	12	14	1000	0.8	82	43637