




Linear Cage - Crossed Roller

stainless steel cage

Ball & Needle
Cages



L1008.060-SS

BALL & NEEDLE CAGES

Material

Stainless rollers (440C), stainless cage (AISI 304).

Important Notes

For load ratings calculations the maximum recommended load is 1/3 of the max. static

load.

Order No.	d_1	p_1	h_1	l_1	w_1	No. of rollers	Dyn. load C N max.
L1008.060-SS-0100	6	9	14	100	0.8	10	25989
L1008.060-SS-0200	6	9	14	200	0.8	21	54541
L1008.060-SS-0300	6	9	14	300	0.8	32	83097
L1008.060-SS-0400	6	9	14	400	0.8	43	111652
L1008.060-SS-0500	6	9	14	500	0.8	55	140208
L1008.060-SS-0600	6	9	14	600	0.8	66	168763
L1008.060-SS-0700	6	9	14	700	0.8	77	197319
L1008.060-SS-0800	6	9	14	800	0.8	88	225874
L1008.060-SS-0900	6	9	14	900	0.8	99	254430
L1008.060-SS-1000	6	9	14	1000	0.8	110	282986