




Linear Cage - Crossed Roller plastic cage

Ball & Needle Cages



L1008.090-PR

BALL & NEEDLE CAGES

Material

Steel rollers (100Cr6, class 3, hardened to 60 HRC) retaining cage plastic (PA 12).

Important Notes

For load ratings calculations the maximum recommended load is 1/3 of the max. static

load.

Order No.	d_1	p_1	h_1	l_1	w_1	No. of rollers	Dyn. load C N max.
L1008.090-PR-0100	9	14	20	100	3	6	7800
L1008.090-PR-0200	9	14	20	200	3	13	16900
L1008.090-PR-0300	9	14	20	300	3	20	26000
L1008.090-PR-0400	9	14	20	400	3	28	36400
L1008.090-PR-0500	9	14	20	500	3	35	45500
L1008.090-PR-0600	9	14	20	600	3	42	54600
L1008.090-PR-0700	9	14	20	700	3	49	63700
L1008.090-PR-0800	9	14	20	800	3	56	72800
L1008.090-PR-0900	9	14	20	900	3	63	81900
L1008.090-PR-1000	9	14	20	1000	3	71	92300