




Linear Cage - Crossed Roller

stainless steel cage

Ball & Needle
Cages



L1008.090-SS

BALL & NEEDLE CAGES

Material

Stainless rollers (440C), stainless cage (AISI 304).

Important Notes

For load ratings calculations the maximum recommended load is 1/3 of the max. static

load.

Order No.	d_1	p_1	h_1	l_1	w_1	No. of rollers	Dyn. load C N max.
L1008.090-SS-0100	9	14	20.5	100	1	6	44167
L1008.090-SS-0200	9	14	20.5	200	1	13	95524
L1008.090-SS-0300	9	14	20.5	300	1	20	146881
L1008.090-SS-0400	9	14	20.5	400	1	28	198239
L1008.090-SS-0500	9	14	20.5	500	1	35	249596
L1008.090-SS-0600	9	14	20.5	600	1	42	300953
L1008.090-SS-0700	9	14	20.5	700	1	49	352310
L1008.090-SS-0800	9	14	20.5	800	1	56	403667
L1008.090-SS-0900	9	14	20.5	900	1	63	455024
L1008.090-SS-1000	9	14	20.5	1000	1	70	455024