




Spur Gears - Module 1.25

carbon steel - 8-10 teeth



Standard Spur Gears



R5182

STANDARD SPUR GEARS

Material

Carbon steel (ISO C45).
Accuracy to JIS B 1702-1 (ISO) class 8-9.

Technical Notes

20° pressure angle, full depth tooth.
Amount of backlash when assembling gears = 0,05 - 0,125mm. Rack shift coefficient $x = 0.5$.

cient $x = 0.5$.

Tips

Module 1.25 for gears with 14-120 teeth see R5180, for gears with 8-11 teeth see R5181, for gears with 12-17 teeth see R5183, for gears with 18-120 teeth see R185.

Max. allowable torque (Nm) is based on standard operating conditions (see technical pages) with a safety factor of 1.2. For non standard applications apply a suitable safety factor depending on frequency of use, type of working etc.

Order No.	Module	No. of teeth z	Pitch dia. d_1	d_2	w_1	d_3 tol. H9	l_1	l_2	l_3	Torque Nm max.	Weight g
R5182.125-10	m 1.25	10	Shifted gear *	15.8	15	10	75	20	40	7.11	54.5