





Linear Cage - Needle Roller

Ball & Needle Cages



L1009.120

BALL & NEEDLE CAGES

Material

Needle roller, steel (100Cr6 to DIN5401, grade 28, class 3), retaining cage plastic

(PA 12).

Order No.	d_1	l_2	p_1	h_1	l_1	w_1	No. of rollers
L1009.120-0100	12	30	16	40	100	5	6
L1009.120-0200	12	30	16	40	200	5	12
L1009.120-0300	12	30	16	40	300	5	18
L1009.120-0400	12	30	16	40	400	5	24
L1009.120-0500	12	30	16	40	500	5	30
L1009.120-0600	12	30	16	40	600	5	36
L1009.120-0700	12	30	16	40	700	5	42
L1009.120-0800	12	30	16	40	800	5	48
L1009.120-0900	12	30	16	40	900	5	54
L1009.120-1000	12	30	16	40	1000	5	61