




Needle Roller Linear Cages

Ball & Needle Cages



L1004.HW15

BALL & NEEDLE CAGES

Material

Steel rollers (100Cr6, hardened to 60 HRC), aluminium retaining cage.

Tips

See technical pages for load rating calculations - based on rail size and number of rollers in the system cage.

Technical Notes

Supplied in max. 1 metre lengths.

Order No.	d_1 ± 0.001	p_1	h_1	l_1	w_1	No. of rollers (pairs)	Dyn. load C /pair of rollers N max.	To suit rail
L1004.HW15-0100	2	4.5	6.8	100	15	21	400	L1004.25
L1004.HW15-0200	2	4.5	6.8	200	15	42	800	L1004.25
L1004.HW15-0300	2	4.5	6.8	300	15	63	1200	L1004.25
L1004.HW15-0400	2	4.5	6.8	400	15	84	1600	L1004.25
L1004.HW15-0500	2	4.5	6.8	500	15	105	2000	L1004.25
L1004.HW15-0600	2	4.5	6.8	600	15	126	2400	L1004.25
L1004.HW15-0700	2	4.5	6.8	700	15	147	2800	L1004.25
L1004.HW15-0800	2	4.5	6.8	800	15	168	3280	L1004.25
L1004.HW15-0900	2	4.5	6.8	900	15	189	3600	L1004.25
L1004.HW15-1000	2	4.5	6.8	1000	15	210	4000	L1004.25