




25mm Needle Roller Linear Rail

heavy duty

Linear Guide-ways



L1017.25

LINEAR GUIDEWAYS

Material

Hardened and ground steel (typically 60 HRC).

Technical Notes

For carriages to suit the required load see

part nos. L1017.FN (flanged) and L1017.UN (unflanged).
Supplied with plastic covers for screws.

Tips

These are very heavy duty needle roller

rails and can only be used with corresponding needle roller carriages L1017. For standard linear guideways and carriages see part no. L1016.

Order No.	Rail size	w ₁	h ₁	l ₁	l ₂	For screws	h ₂	d ₁	d ₂	l ₃	Weight kg
L1017.25-0120	25	23	24.5	120	30	M6	9	7	11	14	0.41
L1017.25-0180	25	23	24.5	180	30	M6	9	7	11	14	0.61
L1017.25-0240	25	23	24.5	240	30	M6	9	7	11	14	0.82
L1017.25-0300	25	23	24.5	300	30	M6	9	7	11	14	1.02
L1017.25-0360	25	23	24.5	360	30	M6	9	7	11	14	1.22
L1017.25-0420	25	23	24.5	420	30	M6	9	7	11	14	1.43
L1017.25-0480	25	23	24.5	480	30	M6	9	7	11	14	1.63
L1017.25-0540	25	23	24.5	540	30	M6	9	7	11	14	1.84
L1017.25-0600	25	23	24.5	600	30	M6	9	7	11	14	2.04
L1017.25-0660	25	23	24.5	660	30	M6	9	7	11	14	2.24
L1017.25-0720	25	23	24.5	720	30	M6	9	7	11	14	2.45
L1017.25-0780	25	23	24.5	780	30	M6	9	7	11	14	2.65
L1017.25-0840	25	23	24.5	840	30	M6	9	7	11	14	2.86
L1017.25-0900	25	23	24.5	900	30	M6	9	7	11	14	3.06
L1017.25-0960	25	23	24.5	960	30	M6	9	7	11	14	3.26
L1017.25-1020	25	23	24.5	1020	30	M6	9	7	11	14	3.47
L1017.25-1080	25	23	24.5	1080	30	M6	9	7	11	14	3.67
L1017.25-1140	25	23	24.5	1140	30	M6	9	7	11	14	3.88
L1017.25-1200	25	23	24.5	1200	30	M6	9	7	11	14	4.08
L1017.25-1260	25	23	24.5	1260	30	M6	9	7	11	14	4.28
L1017.25-1320	25	23	24.5	1320	30	M6	9	7	11	14	4.49
L1017.25-1380	25	23	24.5	1380	30	M6	9	7	11	14	4.69
L1017.25-1440	25	23	24.5	1440	30	M6	9	7	11	14	4.90
L1017.25-1500	25	23	24.5	1500	30	M6	9	7	11	14	5.10
L1017.25-1560	25	23	24.5	1560	30	M6	9	7	11	14	5.30
L1017.25-1620	25	23	24.5	1620	30	M6	9	7	11	14	5.51
L1017.25-1680	25	23	24.5	1680	30	M6	9	7	11	14	5.71
L1017.25-1740	25	23	24.5	1740	30	M6	9	7	11	14	5.92
L1017.25-1800	25	23	24.5	1800	30	M6	9	7	11	14	6.12
L1017.25-1860	25	23	24.5	1860	30	M6	9	7	11	14	6.32
L1017.25-1920	25	23	24.5	1920	30	M6	9	7	11	14	6.53
L1017.25-1980	25	23	24.5	1980	30	M6	9	7	11	14	6.73



Order No.	Rail size	w ₁	h ₁	l ₁	l ₂	For screws	h ₂	d ₁	d ₂	l ₃	Weight kg
L1017.25-2040	25	23	24.5	2040	30	M6	9	7	11	14	6.94
L1017.25-2100	25	23	24.5	2100	30	M6	9	7	11	14	7.14
L1017.25-2160	25	23	24.5	2160	30	M6	9	7	11	14	7.34
L1017.25-2220	25	23	24.5	2220	30	M6	9	7	11	14	7.55
L1017.25-2280	25	23	24.5	2280	30	M6	9	7	11	14	7.75
L1017.25-2340	25	23	24.5	2340	30	M6	9	7	11	14	7.96
L1017.25-2400	25	23	24.5	2400	30	M6	9	7	11	14	8.16
L1017.25-2460	25	23	24.5	2460	30	M6	9	7	11	14	8.36
L1017.25-2520	25	23	24.5	2520	30	M6	9	7	11	14	8.57
L1017.25-2580	25	23	24.5	2580	30	M6	9	7	11	14	8.77
L1017.25-2640	25	23	24.5	2640	30	M6	9	7	11	14	8.98
L1017.25-2700	25	23	24.5	2700	30	M6	9	7	11	14	9.18
L1017.25-2760	25	23	24.5	2760	30	M6	9	7	11	14	9.38
L1017.25-2820	25	23	24.5	2820	30	M6	9	7	11	14	9.59
L1017.25-2880	25	23	24.5	2880	30	M6	9	7	11	14	9.79
L1017.25-2940	25	23	24.5	2940	30	M6	9	7	11	14	10.00
L1017.25-3000	25	23	24.5	3000	30	M6	9	7	11	14	10.20
L1017.25-3060	25	23	24.5	3060	30	M6	9	7	11	14	10.40
L1017.25-3120	25	23	24.5	3120	30	M6	9	7	11	14	10.61
L1017.25-3180	25	23	24.5	3180	30	M6	9	7	11	14	10.81
L1017.25-3240	25	23	24.5	3240	30	M6	9	7	11	14	11.02
L1017.25-3300	25	23	24.5	3300	30	M6	9	7	11	14	11.22
L1017.25-3360	25	23	24.5	3360	30	M6	9	7	11	14	11.42
L1017.25-3420	25	23	24.5	3420	30	M6	9	7	11	14	11.63
L1017.25-3480	25	23	24.5	3480	30	M6	9	7	11	14	11.83
L1017.25-3540	25	23	24.5	3540	30	M6	9	7	11	14	12.04
L1017.25-3600	25	23	24.5	3600	30	M6	9	7	11	14	12.24
L1017.25-3660	25	23	24.5	3660	30	M6	9	7	11	14	12.44
L1017.25-3720	25	23	24.5	3720	30	M6	9	7	11	14	12.65
L1017.25-3780	25	23	24.5	3780	30	M6	9	7	11	14	12.85
L1017.25-3840	25	23	24.5	3840	30	M6	9	7	11	14	13.06
L1017.25-3900	25	23	24.5	3900	30	M6	9	7	11	14	13.26
L1017.25-3960	25	23	24.5	3960	30	M6	9	7	11	14	13.46