




Needle Roller Linear Cages

Ball & Needle Cages



L1004.HW20

BALL & NEEDLE CAGES

Material

Steel rollers (100Cr6, hardened to 60 HRC), aluminium retaining cage.

Tips

See technical pages for load rating calculations - based on rail size and number of rollers in the system cages.

Technical Notes

Supplied in max. 1 metre lengths.

Order No.	d_1 ± 0.001	p_1	h_1	l_1	w_1	No. of rollers (pairs)	Dyn. load C /pair of rollers N max.	To suit rail
L1004.HW20-0100	2.5	5.5	9.8	100	20	17	730	L1004.30
L1004.HW20-0200	2.5	5.5	9.8	200	20	34	1460	L1004.30
L1004.HW20-0300	2.5	5.5	9.8	300	20	51	2190	L1004.30
L1004.HW20-0400	2.5	5.5	9.8	400	20	68	2920	L1004.30
L1004.HW20-0500	2.5	5.5	9.8	500	20	85	3650	L1004.30
L1004.HW20-0600	2.5	5.5	9.8	600	20	102	4380	L1004.30
L1004.HW20-0700	2.5	5.5	9.8	700	20	119	5110	L1004.30
L1004.HW20-0800	2.5	5.5	9.8	800	20	136	5840	L1004.30
L1004.HW20-0900	2.5	5.5	9.8	900	20	153	6570	L1004.30
L1004.HW20-1000	2.5	5.5	9.8	1000	20	170	7300	L1004.30