




L1007.090

BALL & NEEDLE CAGES

Material

Ball steel (100Cr6 to DIN 5401, class 3),
ball cage plastic (PA 12).

Can also be supplied with corrosion resistant stainless balls (AISI 304) balls,
plastic balls (POM) or ceramic balls.

Order No.	d ₁	p ₁	h ₁	l ₁	w ₁	d ₂	No. of rollers
L1007.090-0100	9	11.5	15	100	2	9.2	9
L1007.090-0200	9	11.5	15	200	2	9.2	17
L1007.090-0300	9	11.5	15	300	2	9.2	25
L1007.090-0400	9	11.5	15	400	2	9.2	34
L1007.090-0500	9	11.5	15	500	2	9.2	43
L1007.090-0600	9	11.5	15	600	2	9.2	51
L1007.090-0700	9	11.5	15	700	2	9.2	60
L1007.090-0800	9	11.5	15	800	2	9.2	68
L1007.090-0900	9	11.5	15	900	2	9.2	77
L1007.090-1000	9	11.5	15	1000	2	9.2	86