




L1007.120

BALL & NEEDLE CAGES

Material

Ball steel (100Cr6 to DIN 5401, class 3),
ball cage plastic (PA 12).

Can also be supplied with corrosion resistant stainless balls (AISI 304) balls,
plastic balls (POM) or ceramic balls.

Order No.	d ₁	p ₁	h ₁	l ₁	w ₁	d ₂	No. of rollers
L1007.120-0100	12	15	15	100	2.5	12.2	7
L1007.120-0200	12	15	15	200	2.5	12.2	13
L1007.120-0300	12	15	15	300	2.5	12.2	19
L1007.120-0400	12	15	15	400	2.5	12.2	26
L1007.120-0500	12	15	15	500	2.5	12.2	32
L1007.120-0600	12	15	15	600	2.5	12.2	39
L1007.120-0700	12	15	15	700	2.5	12.2	45
L1007.120-0800	12	15	15	800	2.5	12.2	52
L1007.120-0900	12	15	15	900	2.5	12.2	58
L1007.120-1000	12	15	15	1000	2.5	12.2	65